












10250T Series, Components — Contact Blocks

Contact Blocks (Continued)

Table 2-241. Contact Blocks with Fingerproof Shrouds

Symbol	Circuit	Description/ Notes ①	 10250T1CP	Standard	Logic Level
				Pressure Terminals ②	Pressure Terminals ②
				Catalogue Number	Catalogue Number
 Blank No Plunger	1NC	Stack up to 6 blocks (6 circuits) unless otherwise noted.		10250T51P	10250T51EP
 Blank No Plunger	1NO	Stack up to 6 blocks (6 circuits) unless otherwise noted.		10250T53P	10250T53EP
	NO-NC	Stack up to 6 blocks (12 circuits) unless otherwise noted.		10250T1P	10250T1EP
	2NC	Stack up to 6 blocks (12 circuits) unless otherwise noted.		10250T3P	10250T3EP
	2NO	Stack up to 6 blocks (12 circuits) unless otherwise noted.		10250T2P	10250T2EP
Special Function Blocks ④					
 Blank No Plunger	LONC	Late opening NC. Stack up to 6 blocks (6 circuits) unless otherwise noted.		10250T71P ④	10250T71EP ④
	ECNO-NC	Early closing NO and standard NC. Stack up to 6 blocks unless otherwise noted.		10250T47P ④ ⑤	10250T47EP ④
	ECNO-NO	Early closing NO and standard NO. Stack up to 4 blocks unless otherwise noted.		10250T57P ④ ⑤	10250T57EP ④
	2LONC	Two late opening NC contacts. Stack up to 6 blocks unless otherwise noted.		10250T45P ④	10250T45EP ④
	LONC-ECNO	Overlapping contacts. Stack up to 4 blocks unless otherwise noted.		10250T55P ④ ⑤	10250T55EP ④

① All 10250T contact blocks shown are suitable for use on standard 10250T and E34 operators. These contact blocks are not suitable for Class I Division 2 type 10250T or E34 devices.

② To order contact blocks with translucent amber housing, change Suffix P to **CP** in Catalogue Number e.g. 10250T51CP.

③ Contact blocks with spade terminals are limited to a maximum of one contact block per operator and minimum spacing between devices is 2.5" (63.5 mm). Not suitable for use in 10250T or E34 enclosures. Also available in amber housing. Not available with fingerproof shrouds.

④ Special function contact blocks are not suitable for use with roto-push operators, 3-position push-pull operators, or 4-position selector switches.

⑤ ECNO contact blocks are not suitable for use with 2-position joysticks or when operators are used with padlock attachments.