



**HEAVY-DUTY POWER TOOLS**

**GUARANTEED TOUGH.**



**RECIPROCATING SAWS**

36V Cordless Reciprocating Saw Kit    18V Cordless Reciprocating Saw Kit    14.4V Cordless Reciprocating Saw Kit

| SPECIFICATIONS         | DC305K                  | DC385K                  | DW937K                  |
|------------------------|-------------------------|-------------------------|-------------------------|
| Voltage                | 36V                     | 18V                     | 14.4V                   |
| Keyless Blade Clamp    | Yes                     | Yes                     | Yes                     |
| Strokes/Min            | 0-3,000 spm             | 0-3,000 spm             | 0-2,700 spm             |
| 4 Position Blade Clamp | Yes                     | Yes                     | No                      |
| Stroke Length          | 1-1/8"                  | 1-1/8"                  | 7/8"                    |
| Electric Brake         | Yes                     | Yes                     | Yes                     |
| Tool Weight            | 8.4 lbs                 | 8.3 lbs                 | 6 lbs                   |
| Charger/Batteries      | 1 hour / (1) 36V        | 1 hour / (1) 18V XRP™   | 1 hour / (1) 14.4V      |
| Includes               | reciprocating saw blade | reciprocating saw blade | reciprocating saw blade |



**PENCIL VIBRATOR**

18V Cordless Pencil Vibrator Kit

| SPECIFICATIONS        | DC530KA                                 |
|-----------------------|---|
| Voltage               | 18V                                     |
| Vibrator Diameter     | 1-1/8"                                  |
| Shaft Length          | 4'                                      |
| Vibrations Per Minute | 14,000 vpm                              |
| Charger/Batteries     | 1 hour / (2) 18V XRP™                   |
| Includes              | soft-side bag for batteries and charger |



**SDS HAMMERS**

36V Cordless 1" SDS Rotary Hammer Kit    24V Cordless 7/8" SDS Hammer Kit    18V Cordless 7/8" SDS Hammer Kit

| SPECIFICATIONS    | DC233KL                     | DC223KA                     | DC212KA                     |
|-------------------|-----------------------------|-----------------------------|-----------------------------|
| Voltage           | 36V                         | 24V                         | 18V                         |
| No Load Speed     | 0-1,150 rpm                 | 0-1,100 rpm                 | 0-1,100 rpm                 |
| Blows/Min         | 0-4,400 bpm                 | 0-4,100 bpm                 | 0-4,100 bpm                 |
| Concrete Maximum  | 1"                          | 7/8"                        | 7/8"                        |
| Concrete Optimum  | 1/4"-5/8"                   | 5/32"-1/2"                  | 5/32"-1/2"                  |
| Tool Length       | 10.5"                       | 10.5"                       | 10.5"                       |
| Tool Weight       | 7.8 lbs                     | 8.4 lbs                     | 7.6 lbs                     |
| Charger/Batteries | 1 hour / (2) 36V            | 1 hour / (2) 24V            | 1 hour / (2) 18V XRP™       |
| Includes          | 360° side handle, depth rod | 360° side handle, depth rod | 360° side handle, depth rod |



**JIG SAWS**

36V Cordless Jig Saw Kit w/Keyless Blade Change    18V Cordless Jig Saw Kit w/Keyless Blade Change

| SPECIFICATIONS      | DC308K           | DC330K                |
|---------------------|------------------|-----------------------|
| Voltage             | 36V              | 18V                   |
| Strokes/Min         | 0-2,700 spm      | 0-3,000 spm           |
| Stroke Length       | 1"               | 1"                    |
| Keyless Blade Clamp | Yes              | Yes                   |
| Dust Blower         | Yes              | Yes                   |
| Tool Weight         | 7.5 lbs          | 7.5 lbs               |
| Charger/Batteries   | 1 hour / (1) 36V | 1 hour / (1) 18V XRP™ |
| Includes            | jig saw blade    | jig saw blade         |



**CUT-OUT TOOLS**

18V Cordless Cut-Out Tool    14.4V Cordless Cut-Out Tool

| SPECIFICATIONS    | DC530KA   | DC551KA   |
|-------------------|---|---|
| Voltage           | 18V   | 14.4V   |
| No Load Speed     | 26,000 rpm  | 26,000 rpm  |
| Collet Diameter   | 1/4", 1/8"  | 1/4", 1/8"  |
| Adjustable Guide  | Yes   | Yes   |
| Tool Weight       | 4.5 lbs   | 4.2 lbs   |
| Charger/Batteries | 1 hour / (2) 18V XRP™   | 1 hour / (2) 14.4V XRP™   |
| Includes          | 1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets | 1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets |



**SCREWDRIVERS**

18V Cordless Light Gauge Steel Framing Screwdriver    18V Cordless Drywall/Deck Screwdriver Kit    12V Cordless Drywall/Deck Screwdriver Kit    1/4" (6mm) 7.2V Cordless Two-Position Screwdriver Kit

| SPECIFICATIONS    | DC668KA                                       | DC520KA   | DW979K-2  | DW920K-2             |
|-------------------|---|---|---|----------------------|
| Voltage           | 18V   | 18V   | 12V   | 7.2V                 |
| Drive             | 1/4" hex                                      | 1/4" Hex  | 1/4" Hex  | 1/4" Hex             |
| No Load Speed     | 0-900/0-2,700 rpm                             | 0-900/0-2,900 rpm   | 0-800/0-2,300 rpm   | 0-500 rpm            |
| Max. Torque       | 180 in-lbs                                    | 180 in-lbs  | 180 in-lbs  | 80 in-lbs            |
| Capacity (CRS)    | 12-28 ga.                                     | 12 ga.  | 12 ga.  | -                    |
| Tool Weight       | 5.4 lbs                                       | 5.1 lbs   | 4.2 lbs   | 2.5 lbs              |
| Charger/Batteries | 1 hour / (2) 18V XRP™                         | 1 hour / (2) 18V XRP™                                       | 1 hour / (2) 12V  | 1 hour / (2) 7.2V    |
| Includes          | #2 Phillips screwdriver bit, 5/16" nut runner | bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece | bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece | (2) screwdriver bits |

www.DeWALT.com

1-800-4 DEWALT

<PREVIOUS

3 NEXT>