

# SafeSite® LED Linear Fixture

## Class I Div. 2 Ordering Information

Part Number	Length	Type	Voltage	Lens	Initial Fixture Lumens <sup>1,2,3</sup>	Watt	Lumens Per Watt
Class I, Div 2							
LTD3C4D2P	2'		100 - 277V AC	Clear	3,500	33	106
LTD3C4M2P	4'		100 - 277V AC	Clear	7,000	66	106
LTD3C4B2D	2'		100 - 277V AC	Diffused	3,300	33	100
LTD3C4H2D	4'		100 - 277V AC	Diffused	6,600	66	100
Battery Backup							
LSD3C4MEP	4'	Sustained	100 - 277V AC	Clear	7,000	85	85
LSD3C4MNP	4'	Maintained	100 - 277V AC	Clear	7,000	85	85

**Notes:**

<sup>1</sup>Part numbers listed in the above table are cool white. For neutral white models replace the 5th character with **N**. Ex. LSD3**C**4MEP becomes LSD3**N**4MEP

<sup>2</sup>450 Lumens in Battery Backup mode

<sup>3</sup>Expect a 10% reduction in Lumens for 80 CRI minimum fixtures

<sup>4</sup>All lumen values are typical (tolerance +/- 10%)

<sup>5</sup>See application note on page 3 regarding "sustained" and "maintained" battery modes

For Dialight's complete list of DLC qualified products, please click this link: [www.dialight.com/Assets/News\\_And\\_Events/DLC\\_Part\\_Number\\_List.xls](http://www.dialight.com/Assets/News_And_Events/DLC_Part_Number_List.xls)

## Class II Ordering Information

Part Number	Length	Type	CIID1	CIID2	CIID1	CIID2	Voltage	Lens	Initial Fixture Lumens	Watt	Lumens Per Watt
Class II											
LTF3C4D2P	2'		E / F / G	F / G	•	•	100 - 277V AC	Clear	3,500	33	106
LTF3C4M2P	4'		E / F / G	F / G	•	•	100 - 277V AC	Clear	7,000	66	106
LTF3C4B2D	2'		E / F / G	F / G	•	•	100 - 277V AC	Diffused	3,300	33	100
LTF3C4H2D	4'		E / F / G	F / G	•	•	100 - 277V AC	Diffused	6,600	66	100
Battery Backup											
LSF3C4MEP	4'	Sustained	E / F / G	F / G	•	•	100 - 277V AC	Clear	7,000	85	85
LSF3C4MNP	4'	Maintained	E / F / G	F / G	•	•	100 - 277V AC	Clear	7,000	85	85

**Notes:**

<sup>1</sup>Part numbers listed in the above table are cool white. For neutral white models replace the 5th character with **N**. Ex. LTF3**C**4D2P becomes LTF3**N**4D2P

For Dialight's complete list of DLC qualified products, please click this link: [www.dialight.com/Assets/News\\_And\\_Events/DLC\\_Part\\_Number\\_List.xls](http://www.dialight.com/Assets/News_And_Events/DLC_Part_Number_List.xls)

## Class I Div. 1 Ordering Information

Part Number	Length	Voltage	Lens	Initial Fixture Lumens	Watt	Lumens Per Watt
Class I, Div 1						
LSC3C4M3GEX	4'	100 - 277V AC	Clear	7,000	66	106
LSC3C5M3GEX	4'	347 - 480V AC	Clear	7,250	78	93
LSC3C4D3GEX	2'	100 - 277V AC	Clear	3,500	33	106
LSC3C5D3GEX	2'	347 - 480V AC	Clear	3,600	39	92

**Notes:**

<sup>1</sup>Part numbers listed in the above table are cool white. For neutral white models replace the 5th character with **N**. Ex. LSC3**C**4D3GEX becomes LSC3**N**4D3GEX

For Dialight's complete list of DLC qualified products, please click this link: [www.dialight.com/Assets/News\\_And\\_Events/DLC\\_Part\\_Number\\_List.xls](http://www.dialight.com/Assets/News_And_Events/DLC_Part_Number_List.xls)