

Threaded Rigid Conduit and IMC Enlargers and Nipples

Applications





- Male enlargers:
 - Used to adapt an outlet hole to the next larger size of conduit.
- Offset nipples:
 - Provides box to box connection of knockouts
 - Allows misaligned knockout connection by "rolling" the offset nipple until aligned with each knockout
- Bushed nipples:
 - Used through knockout to connect box to conduit coupling
 - Used with a locknut to connect two boxes side by side or back to back
 - Used with a locknut to connect fixture housings and continuous runs

Material/Finish

- Male enlargers: turned steel
- Offset nipples: malleable iron/zinc plated
- Bushed nipples: zinc diecast/malleable iron/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14814
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 065178
- NEMA: FB-1

| | Catalog Number | Trade Size (Inches) | Dimensions in Inches/Millimeters | | | Weight Lbs./Kgs. Per 100 | |
|---|--------------------|---------------------|----------------------------------|-----------|-----------|--------------------------|---|
| | | | A | B | C | | |
| Male Enlargers † — Turned Steel ‡ | | | | | | | |
|  | ME50-75 † | 3/4F x 1/2M | 0.56/14.2 | 0.78/19.8 | 1.38/35.1 | 16.00/7.26 |  |
| | ME75-100 † | 1F x 3/4M | 0.50/12.7 | 0.94/23.9 | 1.75/44.5 | 26.00/11.80 | |
| | ME100-125 † | 1-1/4F x 1M | 0.56/14.2 | 1.06/26.9 | 2.25/57.2 | 47.00/21.32 | |
| Offset Nipples — Malleable Iron/Zinc Plated | | | | | | | |
|  | OFN-50 | 1/2 | 1.63/41.4 | 0.44/11.2 | 0.75/19.1 | 23.00/10.43 |  |
| | OFN-75 | 3/4 | 1.63/41.4 | 0.44/11.2 | 0.75/19.1 | 31.00/14.06 | |
| | OFN-100 | 1 | 1.63/41.4 | 0.50/12.7 | 0.75/19.1 | 44.00/19.96 | |
| | OFN-125 | 1-1/4 | 1.63/41.4 | 0.56/14.2 | 0.75/19.1 | 60.00/27.22 | |
| | OFN-150 | 1-1/2 | 1.63/41.4 | 0.63/16.0 | 0.75/19.1 | 82.00/37.19 | |
| | OFN-200 | 2 | 1.63/41.4 | 0.75/19.1 | 0.75/19.1 | 112.00/50.80 | |

† Not UL Listed.
‡ Not CSA Certified.