



Powering Business Worldwide

pe.eaton.com

H-Max Drive

HMX34AG20522-N

UPC:786685473840

Dimensions:

- **Height:** 38.02 IN
- **Length:** 13.76 IN
- **Width:** 11.42 IN

Weight:154.3 LB

Notes:All boards are varnished. Corrosion resistant. Battery included in all drives for real-time clock. Keypad kit includes HOA bypass. Keypad kit includes HOA, back reset for Europe application. EMI/RFI filters included. DC link choke included.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** EMC C2
- **Keypad:** Graphical panel
- **Amperage Rating:** 205A
- **Enclosure:** Open NEMA Type 2 IP54
- **Frame Size:** 8
- **Horsepower:** 150 hp
- **Phase:** Three-phase
- **Software:** A
- **Voltage Rating:** 380-480V

Supporting documents:

- [Eaton H-Max HVAC Drives](#)
- [HMX_\(FR8\)2D PDF](#)
- [HMX_\(FR8\) 3D Model Xchange](#)
- [Eatons Volume 6-Solid-State Motor Control](#)



- [H-Max Series Adjustable Frequency Drive Installation Manual](#)
- [Variable frequency drive - Product overview](#)
- [HMX_\(FR8\) 3D Inventor](#)
- [Eaton Specification Sheet - HMX34AG20522-N](#)
- [HMX_\(FR8\) AutoCAD 2D Footprint](#)
- [HMX_\(FR8\) AutoCAD 2D Footprint \(mm\)](#)
- [HMX_\(FR8\) 2D Drawing Xchange](#)

Certifications:

- UL 508C
- EN 61800-5-1
- cUL Certified
- IEC 61800-5-1

Product compliance:

- CE Marked