

NEER Zinc 90° Corner Pulling Elbows

For EMT.

THL: 90° Female/Female

Application

- 90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of EMT. The removable cover gives ample access so that wire pulling can be achieved without any obstructions.

Material/Finish

- Zinc die cast

Certifications and Compliances

- UL Standard: 514B
- CSA Standard: C22.2 No. 18.3
- NEMA: FB-1

CPL: 90° Set Screw

Application

- 90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of EMT. These products are used where it is essential to make tight turns within limited space.

Material/Finish


- Zinc die cast

Certifications and Compliances


- UL Standard: 514B
- CSA Standard: C22.2 No. 18.3
- NEMA: FB-1



THL-500



CPL-50



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	THL-500	1.31/33.3	0.93/23.6
1/2	THL-500G *	1.31/33.3	0.93/23.6
3/4	THL-750	1.40/35.6	1.18/30.0
3/4	THL-750G *	1.40/35.6	1.18/30.0

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	CPL-50	2.30/58.4	2.30/58.4
3/4	CPL-75	2.61/66.3	2.61/66.3

* Provided with neoprene gasket.