



Powering Business Worldwide

pe.eaton.com

E55 Tubular Plastic Body Inductive Proximity Sensor

E55CAL12A2E

UPC:782113888040

Dimensions:

- **Height:** 2.17 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.1438 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 150 mA at 250 Vac
- **Cable Type:** PVC
- **Contact Configuration:** 2 - Wire AC, Normally Open
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Polybutylene Teraphtalate (PBT)
- **Environmental Rating:** NEMA 3, 3S, 4, 4X, 13, (IP66)
- **Input Voltage:** 20-250 Vac
- **Led Indicators:** Output Status
- **Maximum Ac Current:** 150 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E55CAL12A2E](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.