

NEER Zinc Cable Connectors

TA-38: Saddle Clamp

Application

- To terminate armored cable, metal-clad cable or nonmetallic sheathed cable in a 1/2" knockout in a dry location box or enclosure.

Feature

- Furnished with locknut.

Standard Material

- Zinc diecast

Certifications and Compliances


- UL Standard: 514B
- UL Listed: E25014
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1

Note:

- TA-38 is listed for use with 14-2 AWG (nominal O.D. 0.47in./11.9mm.) to 10-3 AWG (nominal O.D. 0.50in./12.7mm.) steel armored cable (AC); 14-2 AWG (nominal O.D. 0.48in./12.2mm.) to 10-3 AWG (nominal O.D. 0.59in./14.9mm.) aluminum armored cable (AC); 0.48in. 12.2mm./ to 0.60in./15.2mm. O.D. steel interlocking metal-clad cable (MCI); 0.47in./11.9mm. to 0.61in./15.5mm. O.D. aluminum interlocking metal-clad cable (MCI); 0.45in./11.4mm. to 0.58in./14.7mm. O.D. aluminum interlocking metal-clad cable, grounding type (MCI-A); 12-2 AWG to 10-3 AWG nonmetallic sheathed cable.



TA-38



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		
		A	B	C
3/8 (1/2 knockout)	TA-38	0.36/9.1	0.90/22.9	0.65/16.5

C-550: Set Screw

Application

- To terminate armored cable or metal-clad cable in a 1/2" knockout in a dry location box or enclosure.

Feature

- Furnished with locknut.

Standard Material

- Zinc diecast

Certifications and Compliances


- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1

Note:

- C-550 is listed for use with 14-2 AWG (nominal O.D. 0.46in./11.7mm.) to 10-2 AWG (nominal O.D. 0.60in./15.2mm.) steel armored cable (AC) and 14-2 AWG (nominal O.D. 0.47in./11.9mm.) to 10-3 AWG (nominal O.D. 0.60in./15.2mm.) steel interlocking metal-clad cable (MCI).



C-550



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		
		A	B	C
3/8 (1/2 knockout)	C-550	0.78/19.8	0.36/9.1	0.93/23.6