





# Spec 5 Conduit Bodies, Covers and Gaskets

For Rigid Conduit and IMC

NEC/CEC — Suitable for use in the following  
Hazardous Locations:  
Class I, Division 2 per NEC 501.10(B)(4)

Trade Size (Inches)	Max. Wire Fill	C		Max. Wire Fill	LB	
		Malleable Iron ②	Malleable Iron Hot Dip Galvanized		Malleable Iron ②	Malleable Iron Hot Dip Galvanized
						
1/2	①	C-50	C-50G	①	LB-50	LB-50G
3/4	(3) # 6AWG	C-75	C-75G	(3) # 6AWG	LB-75	LB-75G
1	(3) # 4AWG	C-100	C-100G	(3) # 4AWG	LB-100	LB-100G
1-1/4	(3) # 2AWG	C-125	C-125G	(3) # 2AWG	LB-125	LB-125G
1-1/2	(3) # 1/0AWG	C-150	C-150G	(3) # 1/0AWG	LB-150	LB-150G
2	(3) # 4/0AWG	C-200	C-200G	(3) # 4/0AWG	LB-200	LB-200G
2-1/2	(3) 300MCM	C-250	—	(3) 300MCM	LB-250	LB-250G
3	(3) 300MCM	C-300	—	(3) 300MCM	LB-300	LB-300G
3-1/2	(3) 350MCM	C-350	—	(3) 350MCM	LB-350	LB-350G
4	(3) 350MCM	C-400	—	(3) 350MCM	LB-400	LB-400G

Trade Size (Inches)	Max. Wire Fill	T		Max. Wire Fill	TB	
		Malleable Iron ②	Malleable Iron Hot Dip Galvanized		Malleable Iron ②	Malleable Iron Hot Dip Galvanized
						
1/2	①	T-50	T-50G	①	TB-50	TB17-G
3/4	(3) # 6AWG	T-75	T-75G	(3) # 6AWG	TB-75	TB27-G
1	(3) # 4AWG	T-100	T-100G	(3) # 4AWG	TB-100	TB37-G
1-1/4	(3) # 2AWG	T-125	T-125G	(3) # 2AWG	TB-125	TB47-G
1-1/2	(3) # 1AWG	T-150	T-150G	(3) # 1AWG	TB-150	TB57-G
2	(3) # 2/0AWG	T-200	T-200G	(3) # 2/0AWG	TB-200	TB67-G
2-1/2	(3) 300MCM	T-250	T-250G	(3) 300MCM	—	—
3	(3) 300MCM	T-300	T-300G	(3) 300MCM	—	—
3-1/2	(3) 350MCM	T-350	T-350G	(3) 350MCM	—	—
4	(3) 350MCM	T-400	T-400G	(3) 350MCM	—	—

① All 1/2" Max Wire Fill Calculations per the NEC - Annex C - Table C8.

② PVC coating available on select bodies. Add suffix **-PVC** to catalog number.