



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0075E3AFB

UPC:786680550553

Dimensions:

- **Height:** 3.937 IN
- **Length:** 3.504 IN
- **Width:** 2.992 IN

Weight:4 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 208/277V
- **Secondary Voltage:** 120V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 75 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Industrial Control Transformer - C0075E3AFB](#)
- [Eaton Specification Sheet - C0075E3AFB](#)



Certifications:

- UL Listed
- CSA Certified
- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.