



Powering Business Worldwide

pe.eaton.com

22.5 mm, Non-metallic Assembled Indicating Light

E22HL9X4

UPC:782114276969

Dimensions:

- **Height:** 1.5 IN
- **Length:** 3 IN
- **Width:** 4.5 IN

Weight: .07 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Non-metallic Heavy-Duty
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Lamp Voltage:** 24 Vac/dc
- **Led Lamp Number:** Cluster style (non-removable)
- **Lens Color:** Amber
- **Lens Type:** Plastic
- **Series:** E22
- **Style:** 22.5 mm

Supporting documents:

- [Eatons Volume 12-Aftermarket, Renewal Parts and Life Extension Solutions](#)
- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eaton Specification Sheet - E22HL9X4](#)

Certifications:

- IEC 947-5-1 MTTA



- CSA Certified
- UL 508
- Lloyd's Register Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.