



Powering Business Worldwide

pe.eaton.com

35SS-Single-Phase Commercial Meter Stack Modules

35SS120RBC

UPC:786849053024

Dimensions:

- **Height:** 16 IN
- **Length:** 20 IN
- **Width:** 16 IN

Weight:98 LB

Notes:Main tenant feeders can exit top, bottom, or back, If being used in outdoor application and exiting the top, mount Myer type hubs on rainproof cap. 120/240V, single-phase, three-wire systems and 208Y/120V network metering

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Socket Amperage:** 225 A
- **Bus Material:** Aluminum
- **Bus Rating:** 1200 A
- **Bypass:** Test bypass
- **Enclosure:** NEMA 3R
- **Interrupt Rating:** Per installed main breaker rating
- **Number Of Jaws:** Five-jaw
- **Number Of Sockets:** 1
- **Phase:** Three-phase in, single-phase out
- **Phase Balance:** B-C
- **Secondary Circuit Breaker:** EHD2_, CCV2_X, CCVH2_X, CVS2_XMM, CV2_XMM,CVH2_XMM
- **Security:** Ring



- **Voltage Rating:** 120/240V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - 35SS120RBC](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved