



Powering Business Worldwide

pe.eaton.com

Drive Isolation Transformer, Ventilated

MD20E85

UPC:786680001222

Dimensions:

- **Height:** 30 IN
- **Length:** 16.5 IN
- **Width:** 23 IN

Weight:260 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Dry Type Distribution, Drive Isolation Transformer
- **Design:** DT-3
- **Coil Material:** Aluminum windings
- **Frame:** 912B
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 208V
- **Secondary Voltage:** 230Y/133V
- **Tap Size:** 1 at +5% FCAN, 1 at -5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 20 KVA
- **Weathershield:** WS38

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - MD20E85](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.