

Three-Phase Encapsulated—Type EPT, 60 Hz

416 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Style Number
	FCAN	FCBN							
3	—	2 at -5%	EPT	115	FR201	70V	116 (53)	Indoor-Outdoor	Y43G28T03A ①
6	—	2 at -5%	EPT	115	FR200	70V	175 (79)	Indoor-Outdoor	Y43G28T06A ①
9	—	2 at -5%	EPT	115	FR103	70V	190 (86)	Indoor-Outdoor	Y43G28T09A ①
15	—	2 at -5%	EPT	115	FR95	70V	275 (125)	Indoor-Outdoor	Y43G28T15A ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84I	422 (191)	Indoor-Outdoor	Y43M28T30A
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84I	660 (299)	Indoor-Outdoor	Y43M28T45A
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84I	1275 (580)	Indoor-Outdoor	Y43M28T75A ②

440 Delta Volts to 220Y/127 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Style Number
	FCAN	FCBN							
3	—	2 at -5%	EPT	115	FR201	70G	116 (53)	Indoor-Outdoor	Y44G31T03A ①
6	—	2 at -5%	EPT	115	FR200	70G	165 (75)	Indoor-Outdoor	Y44G31T06A ①
9	—	2 at -5%	EPT	115	FR103	70G	166 (75)	Indoor-Outdoor	Y44G31T09A ①
15	—	2 at -5%	EPT	115	FR95	70G	275 (125)	Indoor-Outdoor	Y44G31T15A ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84O	422 (191)	Indoor-Outdoor	Y44M31T30A ②
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84O	660 (299)	Indoor-Outdoor	Y44M31T45A
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84O	1275 (580)	Indoor-Outdoor	Y44M31T75A ②

480 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Style Number
	FCAN	FCBN							
3	—	2 at -5%	EPT	115	FR201	70A	116 (52)	Indoor-Outdoor	Y48G28T03N ①
6	—	2 at -5%	EPT	115	FR200	70A	165 (75)	Indoor-Outdoor	Y48G28T06N ①
6	2 at +2.5%	2 at -2.5%	EPT	115	FR200	72B	165 (75)	Indoor-Outdoor	Y48D28T06N ①
9	—	2 at -5%	EPT	115	FR103	70A	166 (75)	Indoor-Outdoor	Y48G28T09N ①
9	—	4 at -2.5%	EPT	115	FR103	503A	185 (84)	Indoor-Outdoor	Y48J28T09N ①
9	2 at +2.5%	2 at -2.5%	EPT	115	FR103	72B	185 (84)	Indoor-Outdoor	Y48D28T09N ①
15	—	2 at -5%	EPT	115	FR95	70A	275 (125)	Indoor-Outdoor	Y48G28T15N ①
15	—	4 at -2.5%	EPT	115	FR95	503A	275 (125)	Indoor-Outdoor	Y48J28T15N ①
15	2 at +2.5%	2 at -2.5%	EPT	115	FR95	72B	275 (125)	Indoor-Outdoor	Y48D28T15N ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84A	422 (191)	Indoor-Outdoor	Y48M28T30N
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84A	720 (327)	Indoor-Outdoor	Y48M28T45N
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84A	1275 (580)	Indoor-Outdoor	Y48M28T75N ②

480 Delta Volts to 208Y/120 Volts—Copper Windings

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Style Number
	FCAN	FCBN							
15	2 at +2.5%	2 at -2.5%	EPT	115	FR95	72B	300 (136)	Indoor-Outdoor	Y48D28T15CU ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84A	505 (230)	Indoor-Outdoor	Y48M28T30CU
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84A	810 (368)	Indoor-Outdoor	Y48M28T45CU
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84A	1450 (659)	Indoor-Outdoor	Y48M28T75CU ②③

Notes

① T-T (Scott T) connected secondary.

② Floor-mount only.

③ Not CSA certified.

Contact your local Eaton sales office for CE Mark transformer requirements. For other ratings or styles not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on [Page V2-T2-213](#).