



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E53 Series Tubular Capacitive Proximity Sensor

**E53KBL30A2EA**

**UPC:**782114013038

### Dimensions:

- **Height:** 3.94 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

**Weight:**.1688 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 5%
- **Connection:** 4 Pin Dual Key Micro Connector
- **Contact Rating:** 300 mA Solid State Output
- **Contact Configuration:** 2 - Wire AC, Normally Closed
- **Diameter:** 1.18 IN
- **Enclosure Material:** Body: Polyoxymethylene (POM), Mounting Nuts, Nylon 66 (PA66)
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12, 13 (IEC IP65)
- **Input Voltage:** 20–250 Vac
- **Led Indicators:** Output Status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Capacitive Proximity
- **Switch Type:** Capacitive Proximity

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Sensing solutions-versatile, robust and](#)



innovative

- Eaton Specification Sheet - E53KBL30A2EA

**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.