



Powering Business Worldwide

pe.eaton.com

Iprox Series Tubular Inductive Proximity Sensor

E59-M12A105C02-D2

UPC:782116303953

Dimensions:

- **Height:** 2.46 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.1438 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1% of sensing distance
- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 500 mA at 6-30 Vdc, 300 mA at 32-48 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN/PNP Auto Configure, Normally Closed
- **Cord Length:** 79.2 FT
- **Diameter:** .47 IN
- **Enclosure Material:** Tube: Stainless Steel, End Bell: Polycarbonate, Front Cap: Polyphenylene Sulfide
- **Environmental Rating:** NEMA 4,4X,6,6P,12,13,IP67,IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** Green power up turns red when output energized
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset short circuit
- **Sensor Type:** Inductive Proximity



Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [iProx sensors](#)
- [Eaton Specification Sheet - E59-M12A105C02-D2](#)

Certifications: No Data**Product compliance:** No Data

© 2016 Eaton. All rights reserved.