



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Industrial Control Transformer

**C0100E5EFB**

**UPC:**786680421747

### Dimensions:

- **Height:** 4 IN
- **Length:** 6 IN
- **Width:** 3.74 IN

**Weight:**6.1 LB

**Notes:**Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 200/220/440V, 208/230/460V, 240/480V
- **Secondary Voltage:** 23/110V, 24/115V, 25/120V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 100 VA

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)



- [Industrial Control Transformer - C0100E5EFB](#)
- [Eaton Specification Sheet - C0100E5EFB](#)
- [C0100E5EFB 3D Model Xchange](#)
- [C0100E5EFB 2D PDF](#)
- [C0100E5EFB 2D Drawing Xchange](#)
- [C0100E5EFB 3D Inventor](#)

**Certifications:**

- UL Listed
- CSA Certified
- cUL Certified

**Product compliance:**

- RoHS Compliant