



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Harsh Environment Safety Switch with Viewing Window

DH324NDKLW

UPC:782114196403

### Dimensions:

- **Height:** 34.38 IN
- **Length:** 11.5 IN
- **Width:** 16 IN

**Weight:**61 LB

**Notes:**For 2-pole applications; use outside poles of 3-pole switch. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Lower viewing window
- **Type:** Single-Throw
- **Amperage Rating:** 200A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 15 at 240 Vac Std. 1 Ph, 25 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 1 Ph, 60 at 240 Vac TD 3 Ph, 40 at 250 Vdc



**Supporting documents:**

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH324NDKLW](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data