



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0300E3C

UPC:786680420023

Dimensions:

- **Height:** 3.819 IN
- **Length:** 5.118 IN
- **Width:** 4.488 IN

Weight:11.7 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 230/460/575V
- **Secondary Voltage:** 115/95V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 300 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - C0300E3C](#)

Certifications:

- CSA Certified
- cUL Certified



- UL Listed

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.