



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0350E6U

UPC:786680019142

Dimensions:

- **Height:** 4.449 IN
- **Length:** 5.63 IN
- **Width:** 5.236 IN

Weight:18.6 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 240/416/480/600V, 230/400/460/575V, 220/380/440/550V, 208/500V
- **Secondary Voltage:** 99/120/130V, 95/115/125V, 91/110/120V, 85/100/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 350 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [C0350E6U 2D Drawing Xchange](#)



- [Eaton Specification Sheet - C0350E6U](#)
- [C0350E6U AutoCAD 2D Footprint \(mm\)](#)
- [C0350E6U AutoCAD 2D Footprint](#)
- [C0350E6U 3D Inventor](#)
- [C0350E6U 2D PDF](#)
- [C0350E6U 3D Model Xchange](#)

Certifications:

- CSA Certified
- UL Listed
- cUL Certified

Product compliance:

- RoHS Compliant