



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 10316 Series, Hazardous Location Limit Switch

10316H1194

UPC:782113451732

### Dimensions:

- **Height:** 5 IN
- **Length:** 3.22 IN
- **Width:** 2.25 IN

**Weight:**1.6813 LB

**Notes:**1N.O.-1N.C. contacts must be same polarity when both circuits are used - 1N.O.-1N.C. contacts have isolated poles and may be used on opposite polarity. Contact factory for availability of CSA &CE approval status.

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 0.2A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 7 Division I Class I BCD, NEMA 9 Division I Class II EFG
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.2A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Side Push Vertical Roller

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H1194](#)

### Certifications:

- UL Listed



- CSA Certified

**Product compliance:**

- CE Marked
- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.