



Powering Business Worldwide

pe.eaton.com

10316 Series, Hazardous Location Limit Switch

10316H1237

UPC:782113451978

Dimensions:

- **Height:** 9.44 IN
- **Length:** 2.25 IN
- **Width:** 2.25 IN

Weight:1.6813 LB

Notes:1N.O.-1N.C. contacts must be same polarity when both circuits are used. Travel with force applied at 1inch (25.4 mm) radius. Applied at end of operator; travel is approximately 14. Call factory for availability of CSA &CE approval status.

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 0.2A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 7 Division I Class I BCD, NEMA 9 Division I Class II EFG
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.2A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Wobble Stick, Spring Coil

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H1237](#)

Certifications:

- CSA Certified



- UL Listed

Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.