



Powering Business Worldwide

pe.eaton.com

E57 Two-Wire Series Tubular Inductive Proximity Sensor

E57-18LE20-A1

UPC:782113933429

Dimensions:

- **Height:** 2.6 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.2938 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3% of sensing distance
- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 300 mA at 132 Vac
- **Cable Type:** PVC
- **Contact Configuration:** 2 - Wire AC, Normally Closed
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Tube: Stainless Steel, End Bell: Polycarbonate, Front Cap: Polyphenylene Sulfide
- **Environmental Rating:** NEMA 4,4X,6,6P,12,13,IP67,IP69K
- **Input Voltage:** 20-132 Vac
- **Led Indicators:** Green power up turns red when output energized
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Non-embeddable
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Inductive Proximity



Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57-18LE20-A1](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.