



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0150E6UFB

UPC:786680023804

Dimensions:

- **Height:** 5.197 IN
- **Length:** 4.449 IN
- **Width:** 4.488 IN

Weight:9 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 240/416/480/600V, 230/400/460/575V, 220/380/440/550V, 208/500V
- **Secondary Voltage:** 99/120/130V, 95/115/125V, 91/110/120V, 85/100/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 150 VA

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator](#)



Interface and Connectivity Solutions

- [C0150E6UFB 2D Drawing Xchange](#)
- [Eaton Specification Sheet - C0150E6UFB](#)
- [C0150E6UFB AutoCAD 2D Footprint \(mm\)](#)
- [C0150E6UFB AutoCAD 2D Footprint](#)
- [C0150E6UFB 3D Inventor](#)
- [C0150E6UFB 2D PDF](#)
- [C0150E6UFB 3D Model Xchange](#)

Certifications:

- CSA Certified
- cUL Certified
- UL Listed

Product compliance:

- RoHS Compliant