



Powering Business Worldwide

pe.eaton.com

Meter Breaker Commercial Safety Sockets

CHU217MTBMS15

UPC:782116165025

Dimensions:

- **Height:** 6 IN
- **Length:** 26 IN
- **Width:** 20 IN

Weight:39 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 100A
- **Feed Type:** Underground
- **Interrupt Rating:** 14 kAIC
- **Main Circuit Breaker:** EHD3100
- **Number Of Jaws:** Seven-jaw
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 480/277V
- **Wire Size:** #14-2/0 AWG

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHU217MTBMS15](#)

Certifications:

- UL Listed

Product compliance: No Data



