

BHHR6PL HORIZONTAL FLUORESCENT HOUSING


Project Name

Type


6 INCH HORIZONTAL FLUORESCENT HOUSING



TRIM: 6501 REFLECTOR



- A** Min. Height = 5-3/8"
Max. Height = 5-1/2"
- B** Trim Aperture = 6-1/8"
- C** Cut-out = 6-1/2"
- D** Trim Outside Diameter = 7-3/8"
- E** Width = 8"
- F** Length = 12-1/2"



DESCRIPTION:

1. LAMP HOLDER - Aluminum lamp holder effectively provides heat dissipation and ventilation. Unitized optics guarantees proper trim to housing installation. Tool-less installation adjustability from either outside the housing or inside the housing.

2. MOUNTING BRACKET - Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span and can be shortened for 12" joists. They are designed to be hammered directly without using nails or screws and could be fit onto T-Bar spline for easy installation and quick alignment.

3. RETAINING SPRINGS - Precision tooled springs secure trim to mounting frame, for effortless and tool-less installation.

4. JUNCTION BOX/BALLAST - UL and ETL listed for through-branch circuit wiring and has four 1/2" KO's, one 3/4" KO and four Romex knockouts with pry-out slots and strain clamps. Ballast and Junction Box are accessible from below, no tools required. **Ballast supplied is manufactured by Advance Transformer CO, Universal Technologies or Lutron Electronics.**

5. MOUNTING FRAME - Die-formed construction for maximum heat dissipation and rust protection.

OPTICS:

6. REFLECTOR - Self-flanged .050" aluminum reflector with low iridescent finish. Reflector provides 45-degree lamp-to-reflector image cutoff.

7. GROOVE BAFFLE - One-piece aluminum with concentric rings.

8. LENS - Choice of either tempered clear, tempered fresnel, tempered prismatic or tempered frosted lens fastened with two torsion springs for easy re-lamping. ETL/UL listed for wet or damp location.

LISTING:

ETL/UL listed for through-branch circuit wiring and damp locations. Wet location only with lens trims.

Energy Star Qualified Models:

- BHHR6PL-1X13-S-120-AT
- BHHR6PL-1X18-S-120-AT
- BHHR6PL-1X26-S-120-AT
- BHHR6PL-2X13-S-120-AT
- BHHR6PL-2X18-S-120-AT
- BHHR6PL-2X26-S-120-AT

TYPE: _____ PROJECT NAME: _____

BHHR6PL - ITEM SELECTOR: (Please check the boxes below for the option desired)

WATTAGE	BALLAST	VOLTAGE	EMERGENCY OPTIONS	TRIM TYPE & DESCRIPTION	REFLTR.	BAFFLE	
1 LAMP <input type="checkbox"/> 1x9 <input type="checkbox"/> 1x13 <input type="checkbox"/> 1x18 <input type="checkbox"/> 1x26 <input type="checkbox"/> 1x32 <input type="checkbox"/> 1x42	<input type="checkbox"/> (E)Electronic <input type="checkbox"/> (M)Magnetic <input type="checkbox"/> (S)Energy Star ² <input type="checkbox"/> (DBL) Dual Ballast DIMMING <input type="checkbox"/> Adv-7 ³ <input type="checkbox"/> Adv-10 ⁴ <input type="checkbox"/> Lut-H ⁴ (FDB)	<input type="checkbox"/> MVOLT (120/277) <input type="checkbox"/> 120 <input type="checkbox"/> 277	<input type="checkbox"/> EMG 750 ^{5,6} (750 Lum.) <input type="checkbox"/> EMG 1300 ^{5,6} (1300 Lum.) <input type="checkbox"/> INTG-750 ^{5,7} (750 Lum.) <input type="checkbox"/> INTG 1300 ^{5,7} (1300 Lum.) <input type="checkbox"/> EMG-D-750 ^{5,8} (750 Lum.) <input type="checkbox"/> INTG-D-750 ^{5,9} (750 Lum.) <input type="checkbox"/> ICE-1300 ^{5,10} (1300 Lum.) OTHER OPTIONS <input type="checkbox"/> FUSE ¹¹ <input type="checkbox"/> RIF ¹²	<input type="checkbox"/> 6501 Reflector <input type="checkbox"/> 6502 Baffle/Ref. <input type="checkbox"/> 6503 Ref./Fres. Gls. Lns. <input type="checkbox"/> 6504 Ref./Pris. Gls. Lns. <input type="checkbox"/> 6505 Baffle/Fres. Gls. Lns. <input type="checkbox"/> 6506 Baffle/Pris. Gls. Lns. <input type="checkbox"/> 6507 Wall Wash <input type="checkbox"/> 6508 Crossblade <input type="checkbox"/> 6512 Baffle/Frost Gls. Lns. <input type="checkbox"/> 6513 Baffle/Tem. Clr. Gls.	<input type="checkbox"/> 6514 Ref./Frost Gls. Lns. <input type="checkbox"/> 6515 Ref./Tem. Clr. Gls. <input type="checkbox"/> 6516 Ref./Pris. Plas. Lns. <input type="checkbox"/> 6517 Baf./Pris. Plas. Lns. <input type="checkbox"/> 6518 Ref./Tem. Clr. Plas. <input type="checkbox"/> 6519 Ref./Tem. Clr. Gls. <input type="checkbox"/> 6509 Deco Glass Ring <input type="checkbox"/> 6510 Double Ring <input type="checkbox"/> 6511 Triple Ring	<input type="checkbox"/> CL <input type="checkbox"/> SCH** <input type="checkbox"/> SHZ* <input type="checkbox"/> WT <input type="checkbox"/> W <input type="checkbox"/> MB	<input type="checkbox"/> WH <input type="checkbox"/> P GLASS <input type="checkbox"/> Blue <input type="checkbox"/> Green <input type="checkbox"/> Red <input type="checkbox"/> Frost

(1=9W-Available only in Magnetic) (2=S-Electronic Energy Star Ballast, available in 120V only) (3=Adv-7 not available on BHHR6PL-1x9) (4=Adv-10 and Lut-H(FDB) are not available on BHHR6PL-1x9, BHHR6PL-1x13) (5=See page 308-321 for more details)
 (6=EMG-Emergency battery pack w/ remote test switch) (7=INTG-Emergency battery pack w/ integral/reflector test switch) (8=EMG-D-Emergency battery pack w/ remote test switch for damp location)
 (9=INTG-D-Emergency battery pack w/ integral/reflector test switch for damp location) (10=ICE-Emergency battery pack w/ remote test switch operating between -18°C and 55°C) (11=FUSE-Single slow-blow fuse) (12=RIF-Radio interference filter)

Specifications:



Sample of Catalog Number: **BHHR6PL-1X26-E-MVOLT-EMG750-6501-CL-WH**

REFLECTOR CL Clear SHZ Satin Haze Low Indescent	BAFFLE WH White P Black	RING WH Self-Flange White Standard on all trims SCH** Self-Flange Chrome ** Only available on XX01 CL GLASS Only available on XX09, XX10 and XX11 series. SHZ* Satin Haze * Provided w/ satin haze ring only
WT Wheat MB Black W White		

*For custom baffle, reflector, trim ring, glass color and lens options, please consult factory.

6 INCH HORIZONTAL FLUORESCENT TRIMS