

3" LOW VOLTAGE SHALLOW NON-IC SERIES HOUSING

Project Name

Type

BL3E-S


3" MINIATURE LOW VOLTAGE "NOISE-FREE" SHALLOW NON-IC HOUSING



DESIGNED FOR 2" X 4" JOIST CONSTRUCTION
(3-5/8" IN HEIGHT)

DESCRIPTION

Small aperture, low voltage, thermally protected, specification grade recessed housing. For new construction, non-insulated ceilings or where insulation can be kept 3" from the housing. Accommodates up to 35W MR16 lamps.



SPECIFICATION

HOUSING - High temperature painted 22 gauge deep drawn single piece housing. Adjusts vertically in plaster frame to accommodate 1/2" to 1-3/8" ceiling. Accommodates lamps up to 35W depending on trim used.

TRANSFORMER - Class II dimming electronic transformer enhanced in heat dissipating cover attached to junction box cover.

BAR HANGERS - Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span and can be shortened for 12" joists. They contain a double-headed real nail for secure attachment into the joist. Bar hanger nails are installed on a 20° downward angle for better contact, and the 90° pivoting mounting plate makes installation fast and accurate. Bar hangers can fit onto T-Bar spline with additional slots and holes for special mounting methods if necessary.

JUNCTION BOX - ETL listed for through-branch circuit wiring and has four 1/2" KOs, one 3/4" KO and four Romex knockouts with true pry-out slots and strain clamps.

ETL and C-ETL listed

For Damp location
For Feed-through wiring



OPTION

1. AIR-SHUT-

• Gasket to prevent air flow from heated or air conditioned spaces.

• Meets all national air flow requirements.

TYPE	WATTAGE	BALLAST	VOLTAGE	OPTION
BL3E-S	<input type="checkbox"/> 20W	<input type="checkbox"/> E=Electronic	<input type="checkbox"/> 120	<input type="checkbox"/> AT Air-Shut
	<input type="checkbox"/> 35W		<input type="checkbox"/> 277	



BL3RE-S


3" MINIATURE LOW VOLTAGE "NOISE-FREE" SHALLOW NON-IC REMODEL HOUSING



DESIGNED FOR 2" X 4" JOIST CONSTRUCTION
(3-5/8" IN HEIGHT)

DESCRIPTION

Small aperture, low voltage, thermally protected remodel housing. For fast and easy installation in existing plaster or mechanical ceilings from 1/2" to 1-3/8" thick. Three remodel clips are easily retractable for fixture removal if necessary.



SPECIFICATION

HOUSING - High temperature painted 22 gauge deep drawn single piece housing. Accommodates lamps up to 35W depending on trim used.

TRANSFORMER - Class II dimming electronic transformer enhanced in heat dissipating cover attached to junction box.

JUNCTION BOX - ETL listed for through-branch circuit wiring and has four 1/2" KOs, one 3/4" KO and four Romex knockouts with true pry-out slots and strain clamps.

INSTALLATION - Three preinstalled spring clips which secure the housing firmly into ceiling to accommodate different ceiling thickness from 1/2" to 1-3/8". and strain clamps.

OPTION

1. AIR-SHUT-

• Gasket to prevent air flow from heated or air conditioned spaces.

• Meets all national air flow requirements.

ETL and C-ETL listed

For Damp location
For Feed-through wiring



TYPE	WATTAGE	BALLAST	VOLTAGE	OPTION
BL3RE-S	<input type="checkbox"/> 20W	<input type="checkbox"/> E=Electronic	<input type="checkbox"/> 120	<input type="checkbox"/> AT Air-Shut
	<input type="checkbox"/> 35W		<input type="checkbox"/> 277	

