


STRUCTURAL ATTACHMENT CD-SERIES

One-piece Pipe Clip

- Size Range: 1/2" through 2"
- Surface Finish: Electro-zinc plated
- May be used for either vertical or horizontal installations



Part Number	Flange Thickness	Bolt Size	Max. Rec. Load (lbs)
CD0B	1/2"	1/4"	250
CD1B	3/4"	1/4"	250
CD2B	1"	1/4"	250
CD3B	1-1/4"	1/4"	250
CD4B	1-1/2"	5/16"	350
CD5B	2"	5/16"	350
CD6B	2-1/2"	5/16"	350
CD7B	3"	5/16"	350
CD8B	3-1/2"	5/16"	350
CD9B	4"	5/16"	350
CD0B37	1/2"	3/8"	250
CD1B37	3/4"	3/8"	250
CD2B37	1"	3/8"	250
CD3B37	1-1/4"	3/8"	250
CD4B37	1-1/2"	3/8"	350
CD5B37	2"	3/8"	350



DIMENSIONAL LEGEND

A Adjustment	BS Bolt Size
CL Center Line	H Height
HS Hole Size	ID Inside Diameter
L Length	MRI Minimum Rod Insertion
OD Outside Diameter	PS Pipe Size
R Radius	RS Rod Size
T Thickness	W Width

MATERIAL USED

CAST IRON:

Grey Cast Iron, ANSI®/ASTM® A 48-76, Class #20

MALLEABLE IRON:

ANSI/ASTM A 47-77, Grade Number 32510

SPRING STEEL:

High Carbon Steel, tempered.

STAINLESS STEEL:

(S4) ANSI Type 304 Stainless Steel: (S6) ANSI Type 316, ASTM A240

STEEL:

- M1020 Merchant Bar Quality, ANSI/ASTM A 36
- Prime Quality, Low Carbon, Hot Rolled Sheet, (may be Pickled and Oiled) ANSI/ASTM A 569
- Commercial Quality, Low Carbon, Cold Rolled, ANSI/ASTM A 366

INSTALLATION

1. All pipe supports, hangers, intermediate components and structural attachments must **ONLY** be used to support pipe, tubing or conduit as stated herein and are **NEVER** to be used for any other purpose.
2. All pipe supports and hangers are designed **ONLY** for **STATIONARY** piping unless otherwise noted.
3. All supports, hangers, clamps and accessories shown to use two nuts on the hanger rod or a jam nut must have nuts tightened securely to assure proper performance.

FINISHES

Standard Finish on all products is plain without coating unless noted. Alternative finishes may be available upon request.

CADDY® COAT:

Electrostatic coating.

COPPER:

CP Copper electroplate (no corrosion protection; for identification purposes only).
(Alternate finish is CADDY COAT.)

EPOXY: EP

LAMINATE:

FL Felt Lined

PAINTED:

RO Red Oxide Primer
PT Painted (Color may vary)

PLAIN:

PL Plain without coating

POLYMER: (normally applied by fluidized bed process, 5 mil minimum thickness)

PVC (VC) Polyvinyl Chloride

ZINC:

EG Zinc electroplate (ANSI/ASTM B 633)

PRE-GAL (PG) Continuous mill annealed and galvanized. Cut edges and welded areas are not zinc coated. Zinc near the uncoated metal becomes a sacrificial anode which protects the bare areas after exposure (ANSI/ASTM A 525 and 526).
HDG (HD) Hot Dipped Galvanization after fabrication; submerged in a bath of molten zinc; forms a metallurgical bond covering all surfaces (ANSI/ASTM A 123).

ZP Zinc and Phosphate coatings combined to provide a corrosion resistant barrier to resist rusting in accordance with ASTM B117-61 Federal Test Number QQM-151.

All dimensions are in inches unless otherwise noted.





See page 263 for finish and material descriptions. All material is Electro-Galvanized Steel unless otherwise noted.





CD SERIES CONDUIT CLIP

Conduit and pipe support for suspension from threaded rod, direct attachment to beam clamps, or direct attachment to structure.



FEATURES

- Fast and easy installation – installs with screwdriver or nut driver.
- Now with Slotted, Hex, Phillips, Robertson combo head.
- Accommodates 1/2" thru 4" EMT or rigid conduit.
- Mounting hole size CD0 thru CD3 for 1/4" bolt. CD4 thru CD9 for 5/16" bolt.
- Retained bolt and built-in nut means there are less parts to handle or drop. Electrogalvanized zinc finish.
- Can be used in all locations where EMT or rigid conduit is used.

INSTALLATION TOOLS



Mild Steel	Coating	Stainless Steel	Material	RS	PS		Box	Lbs.	kN
					Rigid	EMT			
CD0B*	EG	CD0BSS	SS	1/4"	1/2"	1/2"	100	250	1.10
CD1B*	EG	CD1BSS	SS	1/4"	3/4"	3/4"	100	250	1.10
CD2B*	EG	CD2BSS	SS	1/4"	1	1	100	250	1.10
CD2.5B*	EG	CD2.5BSS	SS	1/4"	-	1-1/4"	100	250	1.10
CD3B*	EG	CD3BSS	SS	1/4"	1-1/4"	1-1/2"	100	250	1.10
CD4B*	EG	CD4BSS	SS	5/16"	1-1/2"	-	50	350	1.50
CD5B*	EG	CD5BSS	SS	5/16"	2	2	50	350	1.50
CD6B	EG	CD6BSS	SS	5/16"	2-1/2"	2-1/2"	25	350	1.50
CD7B	EG	CD7BSS	SS	5/16"	3	3	25	350	1.50
CD8B	EG	CD8BSS	SS	5/16"	3-1/2"	3-1/2"	10	350	1.50
CD9B	EG	CD9BSS	SS	5/16"	4	4	10	350	1.50

*Manufactured with retained bolt and built-in nut.

Also available in stainless steel 302.
Contact factory for price and delivery.
To order add suffix **SS** (ie. CD2B-**SS**).
Stainless does not have nutless feature.

CONDUIT SUPPORTS