



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Industrial Control Transformer

**C0100E6UFB**

**UPC:**782116062133

### Dimensions:

- **Height:** 4.567 IN
- **Length:** 4.606 IN
- **Width:** 3.74 IN

**Weight:**6.8 LB

**Notes:**Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for non-rejection type fuses
- **Primary Voltage:** 240/416/480/600V, 230/400/460/575V, 220/380/440/550V, 208/500V
- **Secondary Voltage:** 99/120/130V, 95/115/125V, 91/110/120V, 85/100/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 100 VA

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator](#)



#### Interface and Connectivity Solutions

- C0100E6UFB 2D Drawing Xchange
- Eaton Specification Sheet - C0100E6UFB
- C0100E6UFB AutoCAD 2D Footprint
- C0100E6UFB 3D Inventor
- C0100E6UFB 2D PDF
- C0100E6UFB 3D Model Xchange
- C0100E6UFB AutoCAD 2D Footprint (mm)

#### **Certifications:**

- CSA Certified
- cUL Certified
- UL Listed

#### **Product compliance:**

- RoHS Compliant