



Powering Business Worldwide

pe.eaton.com

Inductive Global Proximity Sensor

E57-12GE08-D

UPC:782116072606

Dimensions:

- **Height:** .47 IN
- **Length:** 1.99 IN
- **Width:** .47 IN

Weight:.35 LB

Warranties:

- 1 year

Specifications:

- **Type:** E57
- **Accuracy:** <2.0% sensing range
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Size:** 12 mm
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire DC, NO
- **Cord Length:** 79.2 FT
- **Diameter:** .472440948 MM
- **Enclosure Material:** Nickel plated brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 100 mA
- **Number Of Wires:** 2-wire
- **Operating Mode:** Unshielded
- **Operating Temperature:** 32° to 104°F
- **Protection:** S/C

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-12GE08-D](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.