



Powering Business Worldwide

pe.eaton.com

E53 Series Tubular Capacitive Proximity Sensor

E53KAL18A2S8

UPC:782114629222

Dimensions:

- **Height:** 3.15 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.3936 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 5%
- **Connection:** 26 Ft. (8m) Cable
- **Contact Rating:** 300 mA Solid State Output
- **Cable Type:** PVC
- **Contact Configuration:** 2 - Wire AC, Normally Open
- **Cord Length:** 312 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Body: Polyoxymethylene (POM), Mounting Nuts, Nylon 66 (PA66)
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12, 13 (IEC IP65)
- **Input Voltage:** 20–250 Vac
- **Led Indicators:** Output Status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Capacitive Proximity
- **Switch Type:** Capacitive Proximity

Supporting documents:



- [Eatons Volume 8-Sensing Solutions](#)
- [Sensing solutions-versatile, robust and innovative](#)
- [Eaton Specification Sheet - E53KAL18A2S8](#)

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.