




ISO-TP Low Voltage Insulators, Metric Thread – ISOTP60M16 (548602)



- Halogen free
- High resistance to leakage current
- Great stability of electrical and mechanical parameters
- Fiberglass reinforced
- UL® Recognized in E125470 and evaluated for dielectric withstand rating of 1,500 VAC/DC
- RoHS compliant



Part Number	ISOTP60M16
Article Number	548602
Material	Steel Glass Fibre Reinforced Polyamide
Finish	Electrogalvanized
Working Temperature	-40 to 266 °F
Flammability Rating	UL® 94V-0
Complies With	IEC® 60695-2-12 (Glow Wire Test 960 °C)
Dielectric Strength, IEC 60439.1	3,500 VAC @ 1 min
Dielectric Strength, UL	1,500 VAC/DC
Insulation Voltage	1,000 VAC 1,500 VDC
Height (H)	2.362"
Hex Width (W)	55 mm
Depth (D)	2.48"
Thread Size (TS)	M16
Thread Depth (TD)	0.79"
Diameter (Ø)	1.732"
Static Load 1 (F1)	4,946 lb
Static Load 2 (F2)	2,248 lb
Unit Weight	0.772 lb
Certifications	CE CSA-Comp cURus IEC 61439-1 ISO-TP Insulators

Part Number	ISOTP60M16
	RoHS
Standard Packaging Quantity	25 pc
UPC	78285666799
EAN-13	3479775486024

Creepage and clearance distances need to be in accordance with the relevant application standard.

IEC is a registered trademark of the International Electrotechnical Commission. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

Pentair products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at erico.pentair.com and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2017 Pentair All rights reserved

Pentair, CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are owned by Pentair or its global affiliates.

All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.