

Galileo 8.0 software: An interactive visualization tool



Galileo software for XV O/I panels is an easy-to-learn and yet powerful and extensive project design environment that can be used ideally in all system and machine building applications. Designed for use in many segments, Galileo offers comprehensive project design tools, providing a full range of functions without any graduated restrictions on tags or screens.

Features

- Easy-to-learn and intuitive graphical user interface with a project overview window
- User-friendly project design with project simulation on development PC
- Drag-and-drop positioning of objects, WYSIWYG (what you see is what you get)
- Convenient series assignment of text and images to tag
- Many graphical objects such as bar graph, slide adjuster, graph plotter, curve chart and camera
- Anti-aliased gauge display
- Enhanced password handling with complex password and aging
- Extensive recipe handling
- Alarm handling with time stamp, history and diagnostics support with image display
- Multi-line display of alarm entries
- Text import/export in XML format, for example Excel®
- Brilliant image display, up to 65,536 colors
- Import of 15 different image formats
- Object parameter list, any number of data objects in a screen



▶ **Safe and simple linking to the control level and the office world**



▶ **Seamless project design of all graphical panels, including PC control station**

▶ **Up to eight simultaneous communications, with data bridge function**



Powering Business Worldwide

Sample of protocols available for popular PLCs

| Company | Description |
|---------------|---|
| Allen-Bradley | DF1 / EtherNet/IP |
| Beckhoff | TwinCAT ADS |
| Mitsubishi | A Series |
| Eaton | easy / SucomA / Suconet K / CANopen / CoDeSys / ELC |
| Omron | Host Link |
| Siemens | PPI / MPI / DP Slave / Industrial Ethernet |
| Various | OPC / Modbus® RTU / Modbus TCP/IP / CoDeSys (SymArti) / CANopen (SDO/PDO) / 3964R |
| BACnet | BACnet (2013) |

Software

| Description | Part Number |
|--|--------------|
| Galileo development software single-seat license | SW-GALILEO-S |
| Galileo development software multi-seat license | SW-GALILEO-M |

Galileo-only XV units

| Display Size in Inches | Resolution | Interface | Part Number | Style Number |
|------------------------|------------|-----------|---------------------|--------------|
| 3.5 | 320 x 240 | RS-232 | XV-102-H3-35TQRL-10 | 171158 |
| 3.5 | 320 x 240 | RS-485 | XV-102-H4-35TQRL-10 | 171159 |
| 5.7 | 640 x 480 | RS-232 | XV-102-H3-57TVRL-10 | 171160 |
| 5.7 | 640 x 480 | RS-485 | XV-102-H4-57TVRL-10 | 171161 |
| 7.0 | 800 x 480 | RS-232 | XV-102-H3-70TWRL-10 | 171162 |
| 7.0 | 800 x 480 | RS-485 | XV-102-H4-70TWRL-10 | 171163 |



Development Environment

Run Time

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122 USA
 Eaton.com

© 2013 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. PA048001EN / Z13617
 April 2013

Eaton is a registered trademark
 of Eaton Corporation.

All other trademarks are property
 of their respective owners.