


ENERGIZER NO. X92

AAA



Industry Standard Dimensions




Specifications

- Classification:** "Cylindrical Alkaline"
- Chemical System:** Zinc-Manganese Dioxide (Zn/MnO₂)
(no added mercury or cadmium)
- Designation:** ANSI-24A, IEC-LR03
- Nominal Voltage:** 1.5 volts
- Typical Capacity:** 1,350 mAh* (to 0.8 volts)
(based on 25 mA continuous at 21°C)
- * Varies according to the applied load, temperature, and cutoff voltage.
- Typical IR:** 100-300 milliohms (fresh)
- Operating Temp:** -18°C to 55°C (0°F to 130°F)
- Typical Weight:** 11.5 grams (0.4 oz.)
- Typical Volume:** 3.8 cubic centimeters (0.2 cubic inch)
- Jacket:** Plastic Label
- Shelf Life:** 7 years at 21°C (80% of rated capacity)


Storage/Capacity Characteristics

Effects of Storage at Various Temperatures




Constant Power Performance

Typical Characteristics (21°C)



Constant Current Performance

Typical Characteristics (21°C)



Important Notice

This data sheet contains typical information specific to batteries manufactured at the time of its publication.


Contents herein do not constitute a warranty.

©Eveready Battery Company, Inc. - All Rights Reserved

ENERGIZER NO. X92


Constant Power Performance

Typical Discharge Characteristics (21°C)



Constant Current Performance


Typical Discharge Characteristics (21°C / 0°C / -20°C)



Industry Standard Tests (21°C)


REMOTE

24 ohm 15 sec/min 8 hrs/day




TAPE, GAME, DIGITAL AUDIO

100 mA 1 hr/day




PORTABLE LIGHTING

5.1 ohm LIF



PHOTOFLASH

600 mA 10 sec/min 1 hr/day



Important Notice

This data sheet contains typical information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

©Eveready Battery Company, Inc. - All Rights Reserved