

Dry Type Transformers General Purpose Encapsulated Single-Phase NEMA 3R

Section 10

.050 - 3 kVA Indoor/Outdoor Type QB UL Listed C-UL Listed

| Input Voltage | Output Voltage | kVA | Frequency (Hz) | Taps | Wiring Diagram No. ¹ | Weight (Lbs) | Frame Size | Product Number |
|-----------------|----------------|------|----------------|---------|---------------------------------|--------------|------------|----------------|
| 120 x 240 Volts | 120/240 Volts | 0.05 | 60 Hz | No Taps | 1 | 6 | 6100 | 9T51B0022 |
| 120 x 240 Volts | 120/240 Volts | 0.1 | 60 Hz | No Taps | 1 | 6 | 6200 | 9T51B0024 |
| 120 x 240 Volts | 120/240 Volts | 0.15 | 60 Hz | No Taps | 1 | 10 | 8175 | 9T51B0025 |
| 120 x 240 Volts | 120/240 Volts | 0.25 | 60 Hz | No Taps | 1 | 10 | 8175 | 9T51B0027 |
| 120 x 240 Volts | 120/240 Volts | 0.5 | 60 Hz | No Taps | 1 | 16 | 10200 | 9T51B0028 |
| 120 x 240 Volts | 120/240 Volts | 0.75 | 60 Hz | No Taps | 1 | 25 | 12200 | 9T51B0029 |
| 120 x 240 Volts | 120/240 Volts | 1 | 60 Hz | No Taps | 1 | 25 | 12225 | 9T51B0030 |
| 120 x 240 Volts | 120/240 Volts | 1.5 | 60 Hz | No Taps | 1 | 40 | 14200 | 9T51B0031 |
| 120 x 240 Volts | 120/240 Volts | 2 | 60 Hz | No Taps | 1 | 45 | 14250 | 9T51B0032 |
| 120 x 240 Volts | 120/240 Volts | 3 | 60 Hz | No Taps | 1 | 60 | 14400 | 9T51B0033 |
| 208 Volts | 120/240 Volts | 0.5 | 60 Hz | No Taps | 4 | 16 | 10200 | 9T51B0158 |
| 208 Volts | 120/240 Volts | 0.75 | 60 Hz | No Taps | 4 | 25 | 12200 | 9T51B0159 |
| 208 Volts | 120/240 Volts | 1 | 60 Hz | No Taps | 4 | 25 | 12225 | 9T51B0160 |
| 208 Volts | 120/240 Volts | 2 | 60 Hz | No Taps | 4 | 45 | 14250 | 9T51B0156 |
| 208 Volts | 120/240 Volts | 3 | 60 Hz | No Taps | 4 | 55 | 14350 | 9T51B0157 |

.050 - 3 kVA Indoor/Outdoor Type QB UL Listed C-UL Listed

| Input Voltage | Output Voltage | kVA | Frequency (Hz) | Taps | Wiring Diagram No. ¹ | Weight (Lbs) | Frame Size | Product Number |
|-------------------|----------------|------|----------------|-----------|---------------------------------|--------------|------------|----------------|
| 277 Volts | 120/240 Volts | 0.25 | 60 Hz | (-2 5.1%) | 2 | 10 | 8175 | 9T51B0187 |
| 277 Volts | 120/240 Volts | 0.5 | 60 Hz | (-2 5.1%) | 2 | 16 | 10200 | 9T51B0188 |
| 277 Volts | 120/240 Volts | 0.75 | 60 Hz | (-2 5.1%) | 2 | 25 | 12200 | 9T51B0189 |
| 277 Volts | 120/240 Volts | 1 | 60 Hz | (-2 5.1%) | 2 | 30 | 12275 | 9T51B0190 |
| 277 Volts | 120/240 Volts | 1.5 | 60 Hz | (-2 5.1%) | 2 | 40 | 14200 | 9T51B0191 |
| 277 Volts | 120/240 Volts | 2 | 60 Hz | (-2 5.1%) | 2 | 45 | 14250 | 9T51B0192 |
| 277 Volts | 120/240 Volts | 3 | 60 Hz | (-2 5.1%) | 2 | 55 | 14350 | 9T51B0193 |
| 380/400/416 Volts | 120/240 Volts | 0.05 | 50 Hz | No Taps | 2 | 6 | 6150 | 9T51B0162 |
| 380/400/416 Volts | 120/240 Volts | 0.15 | 50 Hz | No Taps | 2 | 10 | 8175 | 9T51B0165 |
| 380/400/416 Volts | 120/240 Volts | 0.25 | 50 Hz | No Taps | 2 | 10 | 8200 | 9T51B0167 |
| 380/400/416 Volts | 120/240 Volts | 0.5 | 50 Hz | No Taps | 2 | 20 | 10225 | 9T51B0168 |
| 380/400/416 Volts | 120/240 Volts | 0.75 | 50 Hz | No Taps | 2 | 25 | 12200 | 9T51B0169 |
| 380/400/416 Volts | 120/240 Volts | 1 | 50 Hz | No Taps | 2 | 30 | 12275 | 9T51B0170 |
| 380/400/416 Volts | 120/240 Volts | 1.5 | 50 Hz | No Taps | 2 | 40 | 14225 | 9T51B0171 |
| 380/400/416 Volts | 120/240 Volts | 2 | 50 Hz | No Taps | 2 | 50 | 14300 | 9T51B0172 |
| 380/400/416 Volts | 120/240 Volts | 3 | 50 Hz | No Taps | 2 | 60 | 14400 | 9T51B0173 |

¹See page 10-45 for wiring diagrams.

