



MicroStat® Status Indicator

Model MSL

COMPACT STATUS INDICATOR IN WATER-TIGHT ENCLOSURE

- MSL1, MSL2, MSL3 available in 24VAC/DC, 120VAC and 240VAC; MSL4 and MSL5 available in 24VAC/DC and 120VAC
- Factory assembled
- Small footprint — only 2.2" diameter (55.9 mm)
- Vibration-resistant 5.6W wedge lamp
- Surface mount and integrated 3/4-inch NPT pipe mount
- Type 4X enclosure¹
- Indoor Use only
- Optional Sound Module, LED Lamp, Pipe Mount Base and Flasher
- PLC Compatible
- UL and cUL Listed

The Federal Signal MicroStat® is a compact, Type 4X status indicator, Type 1 with optional sounder. Ideal for OEM applications, the MicroStat comes pre-assembled as 1-, 2-, 3-, 4-, or 5-high light units. The user selects combinations from five colors; Amber, Blue, Clear, Green and Red. O-rings between each segment provide a water-tight and dust-tight seal. The MSL1, MSL2, MSL3 are available in 24VAC/DC, 120VAC and 240VAC; the MSL4 and MSL5 are available in 24VAC/DC and 120VAC. The base of each light can be surface or pipe mounted (3/4-inch NPT).

The lenses lock together and snap apart with a simple twisting motion, allowing for easy lamp changes and quick lens resequencing. A rugged vibration-resistant, thick-filament wedge lamp fills each lens with light, providing excellent optical performance.

Wire connections are made through a 2-piece terminal block. The MicroStat is designed to work with PLC outputs including "Triacs".

An optional 100,000-hour LED light source is available in the five colors. This lamp, made of surface mounted LEDs, plugs directly into the same socket as the standard lamp.

An optional sound module can be installed in the top position of any MicroStat. The Sound Module Kit (MSS) consists of a slotted grille and board-mounted piezoelectric horn. The sounder plugs directly into the wedge socket. Sounder is optional as one of the 5-units.

A pipe mount base, pipes and flashers are also available. See page 16 for a complete list of accessories.

Model	Description	Voltage	Operating Current
MSL1	One status segment	24VAC/DC, 120VAC, 240VAC	0.2 amps
MSL2	Two status segments	24VAC/DC, 120VAC, 240VAC	0.4 amps
MSL3	Three status segments	24VAC/DC, 120VAC, 240VAC	0.6 amps
MSL4	Four status segments	24VAC/DC, 120VAC	0.8 amps
MSL5	Five status segments	24VAC/DC, 120VAC	1.0 amps



¹ MSL with optional sounder rated NEMA Type 1.