

# Pilot and Signaling Devices

## Heavy-Duty 22.5 mm Watertight/Oiltight Pilot Lights

### C-2000

Standard

600 VAC Max., 300 VDC Max.

10 Amps Continuous AC, 2.5 Amps Continuous DC

### Selection Process

Select operator below + Select power supply from page 9-100 & 9-101 + Select nameplate, if required, from pages 9-103 to 9-105 = Complete Unit



Standard Pilot Lights

### Standard Operators

| Operator Style            | Lens Type  | Power Supply Type  | Product Number        | List Price GO-10GC |
|---------------------------|------------|--------------------|-----------------------|--------------------|
| Round Polished Chrome     | Diffused   | —                  | P9CL*D                | \$6.00             |
| Round Polished Chrome     | Refracted  | —                  | P9CL*R                | \$6.00             |
| Round Polished Chrome     | Glass lens | —                  | P9CL*V                | \$18.50            |
| Round Polished Chrome     | None       | —                  | P9CL00                | \$5.00             |
| Round Satin Chrome        | Diffused   | —                  | P9ML*D                | \$6.00             |
| Round Satin Chrome        | Refracted  | —                  | P9ML*R                | \$6.00             |
| Round Satin Chrome        | Glass lens | —                  | P9ML*V                | \$18.50            |
| Round Satin Chrome        | None       | —                  | P9ML00                | \$5.00             |
| Round Engineered Plastic  | Diffused   | —                  | P9XL*D                | \$6.00             |
| Round Engineered Plastic  | Refracted  | —                  | P9XL*R                | \$6.00             |
| Round Engineered Plastic  | None       | —                  | P9XL00                | \$5.00             |
| Square Engineered Plastic | Diffused   | —                  | P9SL*D                | \$7.00             |
| Square Engineered Plastic | None       | —                  | P9SL00                | \$6.00             |
| Unibloc                   | Diffused   | Full Voltage-120 V | P9XU*DD0 <sup>1</sup> | \$12.00            |
| Unibloc                   | Refracted  | Full Voltage-120 V | P9XU*RDO <sup>1</sup> | \$12.00            |
| Unibloc                   | Diffused   | Resistor-120 V     | P9XU*DRN <sup>1</sup> | \$23.00            |
| Unibloc                   | Refracted  | Resistor-120 V     | P9XU*RRN <sup>1</sup> | \$23.00            |
| Unibloc                   | None       | Full Voltage-120 V | P9XU00D0 <sup>1</sup> | \$11.00            |
| Unibloc                   | None       | Resistor-120 V     | P9XU00RN <sup>1</sup> | \$22.00            |

<sup>1</sup>Available only as a pilot light, Unibloc combines an indicator light and power source in one unit, producing a savings for the customer. Full-voltage versions do not include lamp; select lamp from page 9-119. Resistor versions are 130V (ac/dc) and include BA9S 130 V/2W lamp.

Replace asterisk (\*) in product number with color code digit from Colors table below.

### \*Colors

| Color       | Red | Green | Yellow | Blue | White | Orange | Clear |
|-------------|-----|-------|--------|------|-------|--------|-------|
| *Color Code | R   | V     | G      | L    | B     | A      | I     |



Specially Marked Diffusers: See page 9-110

Outlines and Dimensions: See page 9-95  
Accessories: See page 9-110 to 9-119  
Technical Data: See page 9-127 to 9-133