



Catalog No. 9T58K3314G34

Description: 9T58 IP C AND C TRANSFORMER

UPC No 783173144893

Products > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

Core and coil transformers for machine tool applications are used to provide voltage to control devices in applications where regulation and minimum space are important.

- Fully encapsulated coil is impervious to moisture
- Pressure plate terminals ensure secure connections
- Terminal board is anchored in the epoxy for greater reliability
- Wide variety of fusing options
- Rugged, high-impact plastic terminal board
- Full head #8 brass screws assure quick, easy terminations with maximum connection integrity
- Copper windings

- Flexible design allows input or output voltage to match any application
- CUL, CE, UL approvals
- Available fuse-clips offer simple, low-cost fusing with terminal block models and minimum space are important.

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	460
SecVoltage	120-29
KVA	0.53 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
SubType	Control Terminal Block
Frequency	60 Hz
FrameSize	10225
Net Weight	12
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
Net Weight	12
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	4.6 in
Depth	5.7 in
Height	3.9 in

Publications

Title	Publication No.	Publication Type
Transformer Outline Drawing Outline drawing in .pdf format.	303B947AAP10225	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.