

# Molded Case Circuit Breakers

## Molded Case Switches

100-1200A

## Section 6

### Molded Case Switches Spectra™ RMS

UL File E-57546, CSA LR 91464, Includes fixed, high-set Instantaneous trip suitable for reverse feed.

Frame Type	Ampere Rating	Switch <sup>1</sup> Product Number	Terminal Lugs for Front Connection (Cu/Al)		Maximum Short Circuit Withstand Rating <sup>2</sup> (kA rms symmetrical)		
			Product Number	Wire Range	240 Vac	480 Vac	600 Vac
SE150	100	SEDA36AN0100	TCAL18	Aluminum: #12-3/0 Copper: #14-3/0	200	100	25
	150	SEDA36AN0150					
SF250	250	SFDA36AN0250	TCAL29	Aluminum: #8-350 kcmil Copper: #8-350 kcmil	200	100	25
SG600	400	SGDA36AN0400	3-pole lug kit TCLK365 <sup>3</sup>	Aluminum: (2) 2/0-500 kcmil or (1) #8-600 kcmil Copper: (2) 2/0-500 kcmil or (1) #8-600 kcmil	200	100	65
	600	SGDA36AN0600					
SK1200	800	SKDA36AN0800	TCAL81	Aluminum: (3) 3/0-500 kcmil Copper: (3) 3/0-500 kcmil	100	65	42
	1000	SKDA36AN1000	TCAL125	Aluminum: (4) 250-500 kcmil Copper: (4) 250-500 kcmil			
	1200	SKDA36AN1200					

Molded Case Switches Nonautomatic Trip, Includes Cu/Al line and load lugs. For optional lugs, see page 6-106 and 6-107.

Type	Ampere Rating	Number of Poles	Voltage Rating	Product Number
TEB	100	1	120 Vac, 125 Vdc	TEB111V100 <sup>4</sup>
TEB	100	2	240 Vac, 250 Vdc	TEB122V100 <sup>4</sup>
TEB	100	3	240 Vac	TEB132V100 <sup>4</sup>
TEB	100	3	240Vac	TEB132VT100 <sup>9</sup>
TED	100	1	277 Vac, 125 Vdc	TED113V100 <sup>4</sup>
TED	100	2	480 Vac, 250 Vdc	TED124V100 <sup>4</sup>
TED	100	3	480Vac, 250Vdc	TED134VT100 <sup>9</sup>
TED	100	3	600Vac	TED136VT100 <sup>9</sup>
TED	100	3	600Vac	TED136VT100A <sup>10</sup>
TED	150	2	480 Vac, 250 Vdc	TED124Y150 <sup>4,5</sup>
TED	150	3	480Vac, 250Vdc	TED134VT150 <sup>9</sup>
TED	150	3	600Vac	TED136VT150 <sup>9</sup>
TFJ	225	2	600 Vac	TFJ226Y225 <sup>4,6</sup>
TFJ	225	3	600 Vac	TFJ236Y225 <sup>6</sup>
TJJ	400	2	600 Vac, 250 Vdc	TJJ426Y400 <sup>7</sup>
TJJ	400	3	600 Vac	TJJ436Y400 <sup>7</sup>

Type	Ampere Rating	Number of Poles	Voltage Rating	Product Number
TFK	225	2	600 Vac, 250 Vdc	TFK226Y225 <sup>6,7,8</sup>
TFK	225	3	600 Vac, 250 Vdc	TFK236Y225 <sup>7,8</sup>
TJK	400	2	600 Vac, 250 Vdc	TJK426Y400 <sup>7</sup>
TJK	400	3	600 Vac, 250 Vdc	TJK436Y400 <sup>7</sup>
TJK	600	2	600 Vac, 250 Vdc	TJK626Y600 <sup>7</sup>
TJK	600	3	600 Vac, 250 Vdc	TJK636Y600 <sup>7</sup>
TKM	800	2	600 Vac, 250 Vdc	TKMA826Y800 <sup>7</sup>
TKM	800	3	600 Vac, 250 Vdc	TKMA836Y800 <sup>7</sup>
TKM	1000	2	600 Vac, 250 Vdc	TKMA2Y1000 <sup>7</sup>
TKM	1000	3	600 Vac, 250 Vdc	TKMA3Y1000 <sup>7</sup>
TKM	1200	2	600 Vac, 250 Vdc	TKMA2Y1200 <sup>7</sup>
TKM	1200	3	600 Vac, 250 Vdc	TKMA3Y1200 <sup>7</sup>

<sup>1</sup>No rating plug required.

<sup>2</sup>The maximum withstand rating is limited by the application to the value set forth in this table or the short circuit rating of the upstream fuse or circuit breaker, whichever is less. The upstream protective device must have an instantaneous trip function or element and its rated ampacity may not exceed the ampere rating of the switch.

<sup>3</sup>Order one kit for either line or load end; two kits required for both.

<sup>4</sup>Internal accessory requires factory installed dummy trip. Specify on order. Accessories not available for one-pole TEB, TED.

<sup>5</sup>Not UL listed.

<sup>6</sup>600 Volts max.

<sup>7</sup>Internal accessory requires factory installed dummy trip unit. See page 6-44 for additional details. Nonautomatic trip unit and dummy trip not UL listed for field installation.

<sup>8</sup>UL listed only when ordered as a complete switch.

<sup>9</sup>Includes factory installed dummy trip for accessory installation.

<sup>10</sup>Includes factory installed dummy trip and TCAL12A lugs.

