

**X\$D Ultra® XP**  
Premium Efficient Explosion Proof

Pricing



Base Mounted-Class I, Group D; Class II, Groups F and G  
Volts: 230/460, 575  
HP: 1.5 – 30

HP	RPM	Volts	NEMA Frame	SF	FLA	Nom. Eff.	Guar. Min. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs)	C Dim. (in)	Notes
1.5	1200	230/460	182T	1.0	4.8/2.4	87.5	86.5	E9601	\$1,043	G6-7XP\$	N	76	15.90	
1.5	1200	575	182T	1.0	1.9	87.5	86.5	E9602	\$1,043	G6-7XP\$	N	76	15.90	
2	1200	230/460	184T	1.0	6.4/3.2	88.5	86.5	E9603	\$1,164	G6-7XP\$	N	101	15.90	
2	1200	575	184T	1.0	2.6	88.5	86.5	E9604	\$1,164	G6-7XP\$	N	101	15.90	
3	3600	230/460	182T	1.0	8.0/4.0	87.5	86.5	E9605	\$1,035	G6-7XP\$	N	76	15.90	
3	3600	575	182T	1.0	3.1	87.5	86.5	E9606	\$1,035	G6-7XP\$	N	76	15.90	
3	1800	230/460	182T	1.0	7.8/3.9	89.5	88.5	E9607	\$1,007	G6-7XP\$	Y	76	15.90	
3	1800	575	182T	1.0	3.2	89.5	88.5	E9608	\$1,007	G6-7XP\$	N	76	15.90	
3	1200	230/460	213T	1.0	8.8/4.4	89.5	88.5	E9678	\$1,415	G6-7XP\$	N	200	20.20	
3	1200	575	213T	1.0	3.5	89.5	88.5	E9610	\$1,415	G6-7XP\$	N	200	20.20	
5	3600	230/460	184T	1.0	14.4/7.2	88.5	87.5	E9611	\$1,229	G6-7XP\$	Y	101	15.90	
5	3600	575	184T	1.0	5.7	88.5	87.5	E9612	\$1,229	G6-7XP\$	N	101	15.90	
5	1800	230/460	184T	1.0	13.2/6.6	89.5	88.5	E9613	\$1,181	G6-7XP\$	Y	101	15.90	
5	1800	575	184T	1.0	5.3	89.5	88.5	E9614	\$1,181	G6-7XP\$	N	101	15.90	
5	1200	230/460	215T	1.0	14.4/7.2	89.5	88.5	E9679	\$2,010	G6-7XP\$	N	220	20.20	
5	1200	575	215T	1.0	5.7	89.5	88.5	E9616	\$2,010	G6-7XP\$	N	220	20.20	
7.5	3600	230/460	213T	1.0	17.2/8.6	91.0	90.2	E9661	\$1,605	G6-7XP\$	Y	200	20.20	
7.5	3600	575	213T	1.0	6.9	91.0	90.2	E9617	\$1,605	G6-7XP\$	N	200	20.20	
7.5	1800	230/460	213T	1.0	18.0/9.0	91.7	91.0	E9669	\$1,595	G6-7XP\$	Y	200	20.20	
7.5	1800	575	213T	1.0	7.2	91.7	91.0	E9618	\$1,595	G6-7XP\$	N	200	20.20	
7.5	1200	230/460	254T	1.0	20.2/10.1	91.7	91.0	E9680	\$2,553	G6-7XP\$	N	315	25.60	
7.5	1200	575	254T	1.0	8.0	91.7	91.0	E9619	\$2,553	G6-7XP\$	N	315	25.60	
10	3600	230/460	215T	1.0	22.4/11.2	91.0	90.2	E9662	\$1,881	G6-7XP\$	Y	220	20.20	
10	3600	575	215T	1.0	9.1	91.0	90.2	E9620	\$1,881	G6-7XP\$	N	220	20.20	
10	1800	230/460	215T	1.0	24.0/12.0	91.7	90.2	E9671	\$1,779	G6-7XP\$	Y	220	20.20	
10	1800	575	215T	1.0	9.5	91.7	90.2	E9621	\$1,779	G6-7XP\$	N	220	20.20	
10	1200	230/460	256T	1.0	26.2/13.1	91.0	90.2	E9686	\$3,132	G6-7XP\$	N	350	25.60	
10	1200	575	256T	1.0	10.5	91.0	90.2	E9622	\$3,132	G6-7XP\$	N	350	25.60	
15	3600	230/460	254T	1.0	35.2/17.6	91.7	91.0	E9663	\$2,468	G6-7XP\$	Y	315	25.59	
15	3600	575	254T	1.0	13.8	91.7	91.0	E9623	\$2,468	G6-7XP\$	N	315	25.60	
15	1800	230/460	254T	1.0	36.6/18.3	92.4	91.7	E9672	\$2,340	G6-7XP\$	Y	315	25.60	
15	1800	575	254T	1.0	14.6	92.4	91.7	E9624	\$2,340	G6-7XP\$	N	315	25.60	
15	1200	230/460	284T	1.0	36.8/18.4	91.7	91.0	E9682	\$4,167	G6-7XP\$	N	460	28.60	
15	1200	575	284T	1.0	14.7	91.7	91.0	E9625	\$4,167	G6-7XP\$	N	460	28.60	
20	3600	230/460	256T	1.0	45.2/22.6	91.0	90.2	E9664	\$2,972	G6-7XP\$	Y	350	25.60	
20	3600	575	256T	1.0	18.1	91.0	90.2	E9626	\$2,972	G6-7XP\$	N	350	25.60	
20	1800	230/460	256T	1.0	48.0/24.0	93.0	91.7	E9673	\$2,796	G6-7XP\$	Y	350	25.60	
20	1800	575	256T	1.0	19.2	93.0	91.7	E9627	\$2,796	G6-7XP\$	N	350	25.60	
20	1200	230/460	286T	1.0	48.4/24.2	91.7	91.0	E9683	\$5,087	G6-7XP\$	N	510	28.60	
20	1200	575	286T	1.0	19.4	91.7	91.0	E9628	\$5,087	G6-7XP\$	N	510	28.60	
25	3600	230/460	284TS	1.0	55.6/27.8	92.4	91.7	E9665	\$3,723	G6-7XP\$	N	460	27.20	
25	3600	575	284TS	1.0	22.4	92.4	91.7	E9629	\$3,723	G6-7XP\$	N	460	27.20	
25	1800	230/460	284T	1.0	57.8/28.9	93.6	92.4	E9674	\$3,567	G6-7XP\$	Y	460	28.60	
25	1800	575	284T	1.0	23.1	93.6	92.4	E9630	\$3,567	G6-7XP\$	N	460	28.60	
30	3600	230/460	286TS	1.0	67.2/33.6	92.4	91.7	E9666	\$4,377	G6-7XP\$	N	510	27.20	
30	3600	575	286TS	1.0	26.9	92.4	91.7	E9631	\$4,377	G6-7XP\$	N	510	27.20	
30	1800	230/460	286T	1.0	69.4/34.7	93.6	93.0	E9675	\$4,167	G6-7XP\$	Y	510	28.60	
30	1800	575	286T	1.0	27.8	93.6	93.0	E9632	\$4,167	G6-7XP\$	N	510	28.60	