



**Catalog No. SEDA24AT0100**

**Description: SED 2-POLE 240/480V 100 AMP**

**UPC No 783164211139**

**Products > Circuit Breakers > Molded Case Circuit Breakers > Spectra RMS™ Electronic Trip**

Spectra RMS Molded Case Circuit Breakers (SE150, SF250, SG600 and SK1200) have a digital, solid state, RMS sensing trip system with field installable, front-mounted rating plugs to establish or change the breaker ampere rating. Adjustable instantaneous with tracking short-time is standard on all frames. The trip system uses digital sampling to determine the RMS value of sinusoidal and non-sinusoidal currents.

**Descriptors**

Category	Spectra RMS™ Electronic Trip
GO Schedule	ES

**Specifications**

Product Line	Spectra RMS - Standard
Trip Style	Interchangeable
Frame Type	SE150
Amperage	100 A, 70 A, 80 A, 90 A
Poles	2
System Voltage	120 Vac, 120/240 Vac, 240 Vac, 277 Vac, 480 Vac
120 Vac Interrupting Rating	18 KAIC
120/240 Vac Interrupting Rating	18 KAIC
240 Vac Interrupting Rating	18 KAIC
277 Vac Interrupting Rating	18 KAIC
480 Vac Interrupting Rating	18 KAIC
Trip Function	LSI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TCAL18
Long Time	Fixed
Short Time	Adjustable
Instantaneous	Adjustable
Current Metering	No
Protective Relays	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E11592
CSA File#	LR40350

## Publications

Title	Publication No.	Publication Type
<a href="#">SE (100AF 70-150AT); Let-Through Energy</a> 1-page peak let through energy curve.	K215-196A	Time Current Curves
<a href="#">Spectra RMS MCCB, Type SE150 Plug-in Base, Model</a> Full Scale solid model in .stp format for SE150 3P Plug-in Base.	SE-Plug-in-STP	Drawings-Outline and Dimensional
<a href="#">Spectra RMS MCCB, Type SE150, Drawing</a> 1-Page, Fully dimensioned outline drawing in .dxf format. Includes door cut-out.	GEM-2877-DXF	Drawings-Outline and Dimensional
<a href="#">Spectra RMS MCCB, Type SE150, Drawing</a> 1-Page, Fully dimensioned outline drawing in .pdf format. Includes door cut-out.	GEM-2877-PDF	Drawings-Outline and Dimensional
<a href="#">Spectra RMS MCCB, Type SE150, Model</a> Full Scale solid model in .stp format for SE150 Circuit Breakers.	GEM-2877-STP	Drawings-Outline and Dimensional
<a href="#">SE (100AF 70/80RP); Long/Tracking Short Time Instantaneous</a> 1-page time current curve.	K215-169B	Time Current Curves
<a href="#">SE (100AF 90/100RP); Long/Tracking Short Time Instantaneous</a> 1-page time current curve.	K215-170B	Time Current Curves
<a href="#">SE (150AF 100/150AF); Peak Let-Through Current</a> 1-page peak let through current curve.	K215-197A	Time Current Curves

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.