



Catalog No. SG400F

Description: ENCLOSURE NEMA 1 FLUSH 400A

UPC No 783164219500

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker. Spectra® RMS circuit breakers are suitable for use on AC systems only.

Enclosure notes and/or limitation: For 3 phase, 4-wire ground fault, order neutral kit and neutral current sensor kit (kits must be mounted in enclosure).

ACCESSORIES:

Neutral Kit (non-GF applications):TNIA400

Neutral Kit(s) (for GF applications): TNIA400VG

Neutral Current Sensor(s) (for GF applications): TSRG201, TSRG204

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B2

Specifications

Enclosure Type	NEMA Type 1
Mounting	Flush
Frame Type	SG600
Amperage	400 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	208C2891SH1
GSA Compliance	No

Dimensions

Height	31.4 in
Depth	6.6 in
Width	15.2 in
Weight	36.0 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 1 enclosure, 400 amp max. Product Numbers SG400F and SG400S. 1 page outline drawing in .pdf format.	208C2891-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.