



Catalog No. TH2221M

Description: 30A 2P MD N12 240V FUSIBLE

UPC No 783164092592

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Mill

- Designed specifically for the rugged conditions found in steel mills, cement foundries and other process-related environments.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating - field convertible to compression connectors.
- Full cover interlocks.

Descriptors

Category	Mill
GO Schedule	SB

Specifications

Voltage	240 AC
Amperage	30 A
Poles	2
Wires	2
Fusing	Fusible
Enclosure	NEMA 12 Drip/Dust-tight
Options	None
Wire Range (Cu/Al)	14-8 CU;12-8 AL
240 Vac, NEC Std, 1-ph	1.5 hp
240 Vac, Time Delay, 1-ph	3.0 hp
250 Vdc	5.0 hp
GSA Compliance	No

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	11.3 in
Depth	4.7 in
Width	7.4 in
Weight	13.0 lb

Publications

Title	Publication No.	Publication Type
600A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH123	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.