



## Catalog No. 9T58K1978

Description: TFMR 0.5KVA 400-115/230 CTLO/NA CU

UPC No 783173140437

Products > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

Core and coil transformers for machine tool applications are used to provide voltage to control devices in applications where regulation and minimum space are important.

- Fully encapsulated coil is impervious to moisture
- Pressure plate terminals ensure secure connections
- Terminal board is anchored in the epoxy for greater reliability
- Wide variety of fusing options
- Rugged, high-impact plastic terminal board
- Full head #8 brass screws assure quick, easy terminations with maximum connection integrity
- Copper windings
- Flexible design allows input or output voltage to match any application
- CUL, CE, UL approvals
- Available fuse-clips offer simple, low-cost fusing with terminal block models and minimum space are important.

### Descriptors

Category	Control Power
GO Schedule	TQ

### Specifications

Phase	1
PriVoltage	380/400/416
SecVoltage	115/230
KVA	0.50 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
SubType	CONTROL LEADS OUT
Frequency	50 Hz
FrameSize	10225
Net Weight	12
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	None
Net Weight	12
Sound	Std
GSA Compliance	Yes

### Classifications

UL	Yes
----	-----

**Classifications**

cUL	Yes
CE	No

**Dimensions**

Width	4.6 in
Depth	5.7 in
Height	3.9 in

## Publications

Title	Publication No.	Publication Type
<a href="#">Transformer Outline Drawing</a> Outline drawing in .pdf format.	303B947ABP10225	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.