



Catalog No. 9T58K2909

Description: CORE AND COIL SM PWR TRANSFORMERS

UPC No 783173123652

Products > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

Core and coil transformers for machine tool applications are used to provide voltage to control devices in applications where regulation and minimum space are important.

- Fully encapsulated coil is impervious to moisture
- Pressure plate terminals ensure secure connections
- Terminal board is anchored in the epoxy for greater reliability
- Wide variety of fusing options
- Rugged, high-impact plastic terminal board
- Full head #8 brass screws assure quick, easy terminations with maximum connection integrity
- Copper windings
- Flexible design allows input or output voltage to match any application
- CUL, CE, UL approvals
- Available fuse-clips offer simple, low-cost fusing with terminal block models and minimum space are important.

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	120x240
SecVoltage	120/240
KVA	0.20 KVA
Coil Material	CU
TempRise	80.0 °C
ElecShield	N
SubType	Control Terminal Block
Frequency	60 Hz
FrameSize	8175
Net Weight	6
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	None
Net Weight	6
Sound	Std
GSA Compliance	Yes

Classifications

UL	Yes
----	-----

Classifications

cUL	Yes
CE	No

Dimensions

Width	3.8 in
Depth	4.9 in
Height	3.3 in

Publications

Title	Publication No.	Publication Type
Transformer Outline Drawing Outline drawing in .pdf format.	303B947AAP08175	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.