



Catalog No. TH3365SS

Description: 400A 3P HD N4X SS 600V FUSIBLE

UPC No 783164089332

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	400 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 4/4X Water/Dust-tight
Options	None
Wire Range (Cu/Al)	(1) 2-600 or (2) 1/0-250
240 Vac, NEC Std, 3-ph	50.0 hp
240 Vac, Time Delay, 3-ph	125.0 hp
480 Vac, NEC Std, 3-ph	100.0 hp
480 Vac, Time Delay, 3-ph	250.0 hp
600 Vac, NEC Std, 3-ph	125.0 hp
600 Vac, Time Delay, 3-ph	350.0 hp
250 Vdc	50.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	59.5 in
Depth	8.4 in
Width	24.6 in

Dimensions

Weight

131.0 lb

Publications

Title	Publication No.	Publication Type
Spec-Setter Safety Switches 36 page brochure and application guide. General Electric's Spec-Setter safety switches are available for all your disconnect needs, no matter what the application. Stainless Steel Safety Switches Sealed Tight - Latch it!	DET-845	Brochures
2 pages. New over center latch system requires no tools to open the switch. Designed for commercial and industrial applications in corrosive environments where safety, high performance and continuity of service are essential. 600A - Safety Switches	DET-842	Brochures
1 page outline drawing in .pdf format.	10103091-SH119	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.