



## Catalog No. FCN36TE030R

Description: RECORDPLUSMCCB100AFRAMENOLUGS

UPC No 783164322552

Products > Circuit Breakers > Molded Case Circuit Breakers > Record Plus™ Thermal Magnetic Trip

Record Plus® represents the very latest in molded case circuit breaker design. Utilizing design features such as double-break rotary contact structures and advanced ablative materials to enhance interruption, Record Plus® is capable of interrupting ratings up to 200kA (FC max is 150kA). High kAIC ratings, selective coordination, reduced arc flash energy, and current limitation embody the core design principles of Record Plus®. FC 100 circuit breakers are supplied with factory installed non-user interchangeable thermal-magnetic trip units and can be supplied with or without lugs. FC is available in 2- and 3-pole versions, both in a 3-pole footprint.

Record Plus® product numbers ending in R or R0 do not include lugs. An R1 suffix indicates that the breaker is supplied with line and load lugs, R2 indicates load lugs, and R3 indicates line lugs. RV suffixed product numbers include load lugs and line connections specifically designed for General Electric type AD panels. All frames use common internal accessories (auxiliary switches, UV releases, shunt trips, and bell alarms) UL listed for field installation. UL listed maximum short circuit ratings at 480VAC are 150kA for the 100A frames and 200kA for the 600A frames. Unless noted otherwise, all circuit breakers and accessories are listed in UL file number E11592.

### Descriptors

Category	Record Plus™ Thermal Magnetic Trip
GO Schedule	EH

### Specifications

Product Line	Record Plus
Trip Style	Non-Interchangeable
Frame Type	FC100
Amperage	30 A
Poles	3
System Voltage	240 Vac, 250 Vdc, 480 Vac, 500 Vdc, 600 Vac
240 Vac Interrupting Rating	150 KAIC
250 Vdc Interrupting Rating	42 KAIC
480 Vac Interrupting Rating	65 KAIC
500 Vdc Interrupting Rating	40 KAIC
600 Vac Interrupting Rating	25 KAIC
600/347 Vac Interrupting Rating	25 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	FCALK13, FCOLK13
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
Special Markings	HACR
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------

**Classifications**

CSA File#

LR40350

---

## Publications

Title	Publication No.	Publication Type
<a href="#">Record Plus Breaker: FC100 Instructions</a> 4 pages, Rev.06, Installation Instructions	DEH-40463	Installation and Instruction
<a href="#">FB - Peak Let Through Current</a> Peak I2t Curve	DES-030	Time Current Curves
<a href="#">Record Plus MCCB, FC100 Frame, Drawing</a> 1-Page, Non-dimensioned, full-scale layout drawing in .dxf format	FC100-DXF	Drawings-Outline and Dimensional
<a href="#">FB - 30A</a> 30A	DES-016C	Time Current Curves
<a href="#">FB - Let Through Energy Curves</a> Peak Current Curve	DES-031	Time Current Curves
<a href="#">Record Plus MCCB, FC100 Frame, Drawing</a> 1-Page, Fully dimensioned outline drawing in .pdf format	10085772-SH1	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.