



Catalog No. THN3362M

Description: 60A 3P MD N12 600V NONFUSE

UPC No 783164092769

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Mill

- Designed specifically for the rugged conditions found in steel mills, cement foundries and other process-related environments.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating - field convertible to compression connectors.
- Full cover interlocks.

Descriptors

Category	Mill
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 12 Drip/Dust-tight
Options	None
Wire Range (Cu/Al)	14-2
240 Vac, NEC Std, 3-ph	20.0 hp
480 Vac, NEC Std, 1-ph	20.0 hp
480 Vac, NEC Std, 3-ph	50.0 hp
600 Vac, NEC Std, 1-ph	25.0 hp
600 Vac, NEC Std, 3-ph	60.0 hp
600 Vdc	10.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	19.3 in
Depth	5.0 in
Width	9.4 in
Weight	15.0 lb

Publications

Title	Publication No.	Publication Type
600A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH123	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.