

# Pilot and Signaling Devices

## Heavy-Duty 22.5 mm Watertight/Oiltight Selector Switches

## Section 9

### C-2000

2-Position Lever Operated Selector Switches

Non-Illuminated

600 VAC Max., 300 VDC Max.

10 Amps Continuous AC, 2.5 Amps Continuous DC

#### Black Lever 2-Position


Position Type	Operator Style	Release Type	Cam Code	Product Number	List Price GO-10GC
2-Position	Round Polished Chrome	Maintained	D, I, H	P9CSV#0N	\$14.50
2-Position	Round Satin Chrome	Maintained	D, I, H	P9MSV#0N	\$14.50
2-Position	Round Engineered Plastic	Maintained	D, I, H	P9XSV#0N	\$14.50
2-Position	Round Polished Chrome	Spring Return L → C	H	P9CSVH1N	\$16.50
2-Position	Round Satin Chrome	Spring Return L → C	H	P9MSVH1N	\$16.50
2-Position	Round Engineered Plastic	Spring Return L → C	H	P9XSVH1N	\$16.50
2-Position	Round Polished Chrome	Spring Return L ← R	D	P9CSVD5N	\$16.50
2-Position	Round Satin Chrome	Spring Return L ← R	D	P9MSVD5N	\$16.50
2-Position	Round Engineered Plastic	Spring Return L ← R	D	P9XSVVD5N	\$16.50
2-Position	Round Polished Chrome	Spring Return C ← R	I	P9CSVI5N	\$16.50
2-Position	Round Satin Chrome	Spring Return C ← R	I	P9MSVI5N	\$16.50
2-Position	Round Engineered Plastic	Spring Return C ← R	I	P9XSVI5N	\$16.50

Replace double dagger (§) in maintained product number with cam code from cams table below.


#### Cams

Choose desired cam. Note selection and position of contact block(s).

§Cam Code				Quick-Connect Terminal Contact Block			
				Position 1	Position 2	Position 1	Position 2
D	O	—	X	—	P9B10VN	—	P9B10FN
	X	—	O	P9B01VN	—	P9B01FN	—
	O	—	X	—	—	—	—
	X	—	O	P9B11VN	—	—	—
I	—	O	X	—	P9B10VN	—	P9B10FN
	—	X	O	P9B01VN	—	P9B01FN	—
	—	O	X	—	—	—	—
	—	X	O	P9B11VN	—	—	—
H	X	O	—	—	P9B10VN	—	P9B10FN
	O	X	—	P9B01VN	—	P9B01FN	—
	X	O	—	—	—	—	—
	O	X	—	P9B11VN	—	—	—



Operator Positions



Contact Block Positions  
(viewed from rear)



Outlines and Dimensions: See page 9-77  
Accessories: See page 9-102 to 9-111  
Technical Data: See page 9-119 to 9-125