

X\$D Ultra® 841
TEFC—Extra Severe Duty

Pricing (cont.)



Volts: 460, 575
HP: 0.75 - 250

HP	RPM	Volts	Frame	FLA	Nom. Eff.	Guar. Min. Eff.	Cat. No.	List Price	Price Symbol	Norm. Stk.	Wt. (lbs)	C Dim. (in)	Notes
150	1200	460	447T	171.0	95.8	95.4	M9476	\$27,162	G4-7UX	Y	2860	52.12	
150	1200	575	447T	137.0	95.8	95.4	M9385	\$27,162	G4-7UX	N	2860	52.12	
150	900	460	449T	184.0	95.0	94.5	M8937	\$39,158	G4-7UX	N	3150	52.12	
150	900	575	449T	147.0	95.0	94.5	M8938	\$39,158	G4-7UX	N	3120	52.12	
200	3600	460	447TS	214.0	95.8	95.4	M9477	\$29,729	G4-7UX	Y	2560	50.37	66, 112
200	3600	460	447TS	214.0	95.8	95.4	M8978	\$29,729	G4-7UX	Y	2630	50.37	62, 112
200	3600	575	447TS	170.0	95.8	95.4	M8939	\$29,729	G4-7UX	N	2560	50.37	66, 112
200	1800	460	447T	220.0	96.5	96.2	M9478	\$26,421	G4-7UX	Y	2800	54.12	
200	1800	575	447T	175.0	96.5	96.2	M9387	\$26,421	G4-7UX	Y	2800	54.12	
200	1200	460	449T	229.0	95.8	95.4	M8940	\$30,213	G4-7UX	Y	3070	54.12	
200	1200	575	449T	183.0	95.8	95.4	M8941	\$30,213	G4-7UX	N	3070	54.12	
200	900	460	449T	247.0	95.4	95.0	M8942	\$41,250	G4-7UX	N	3120	54.12	97, 113
250	3600	460	449TS	265.0	95.8	95.4	M8943	\$37,578	G4-7UX	Y	2770	50.37	66, 112, 113
250	3600	460	449TS	265.0	95.8	95.4	M8979	\$37,578	G4-7UX	Y	2770	50.37	62, 112, 113
250	3600	575	449TS	211.0	95.8	95.4	M8944	\$37,578	G4-7UX	N	2770	50.37	66, 112, 113
250	1800	460	449T	280.0	96.2	95.8	M8945	\$30,654	G4-7UX	Y	2790	54.12	112
250	1800	575	449T	224.0	96.2	95.8	M8946	\$30,654	G4-7UX	N	2790	54.12	112
250	1200	460	449T	294.0	95.8	95.4	M8947	\$35,990	G4-7UX	Y	3150	54.12	95, 96, 97
250	1200	575	449T	233	95.8	95.4	M9630	\$35,990	G4-7UX	N	3150	54.12	95, 96, 97
300	3600	460	449TS	319.0	95.8	95.4	M8948	\$40,170	G4-7UX	Y	2790	54.12	62, 95, 96, 116
300	1800	460	449T	332.0	96.2	95.8	M8949	\$35,624	G4-7UX	Y	2980	54.12	112
300	1800	575	449T	264	96.2	95.8	M9640	\$35,624	G4-7UX	N	2980	54.12	112

Notes:

- 62 Connected for CCW rotation facing opposite shaft end. No reconnection possible
- 66 CW rotation only facing opposite drive end. CCW rotation available, but must be specified on the order
- 95 Class F temperature rise
- 96 Does not meet IEEE 841 temperature rise
- 97 Does not meet 200C AIT at 1.0SF-215C AIT and above only
- 112 Noise level exceeds IEEE-841
- 113 Bearing temperature exceeds IEEE-841
- 116 Does not meet 200°C AIT at 1.0SF-260°C AIT and above only.

2.23
X\$D Ultra® 841